

NORTON

SAINT-GOBAIN

NORTON NORZON BLUEFIRE F826 FIBER DISCS

Stock Removal

Weld Blending

Cleaning and Finishing

Deburring

NEW



The Better Choice for Super Alloys, Steels, and High-Pressure Applications

Our new NorZon BlueFire ceramic aluminum and zirconia alumina blended fiber discs grind and blend a multitude of hard-to-grind materials. With their fast cut rate and longer life over conventional zirconia products, your productivity will increase as total abrasive cost decreases.



**Exceptional Blend
of Performance
and Price**

NORZON BLUEFIRE F826

BETTER CHOICE FOR SUPER ALLOYS, STEELS, AND HIGH PRESSURE APPLICATIONS


FEATURES

- New, improved blend of patented ceramic alumina and zirconia alumina abrasive

BENEFITS


- Fast, aggressive cutting; 76% better metal removal rate than aluminum oxide and 33% better than competitive zirconia alumina fiber discs
- Self-sharpen with use

CONVENTIONAL FIBER DISCS



The most heavy-duty of coated abrasive discs with resin over resin construction on heavy-duty vulcanized fiber backing. Designed for applications ranging from heavy stock removal to surface blending. Used with back-up pads on portable angle grinders.

SPEED-CHANGE FIBER DISCS



These fiber discs feature Norton quick, tool-free, twist-on and off Speed-Change fasteners. Discs lock to standard back-up pads with a unique nut design and are easily removed, increasing your productivity.

AVOS FIBER DISCS



Patented, see-through design allows interrupted cut which reduces heat up to 30% over standard discs. Scooped holes create air flow to pull swarf away from grinding zone; cool cutting and extended product life. 5° back-up pad for full utilization of discs – no gouging. Quick, tool-free, twist-on and off Speed-Lok fasteners.

NORTON NORZON BLUEFIRE F826 FIBER DISCS



CONVENTIONAL DISC AVAILABILITY



TIER: **BETTER**
 BRAND: Norton
 TRADENAME: **NORZON BLUEFIRE F826**
 ABRASIVE: Ceramic/Zirconia

SIZE (D X H)	GRIT	STD. PKG.	PART NO.
4-1/2 x 7/8	24	25	66261138457
	36		66261138456
	50		66261138454
	60		66261138453
	80		66261138452
5 x 7/8	24	25	66261138563
	36		66261138562
	50		66261138561
	60		66261138601
	80		66261138600
7 x 7/8	24	25	66261138594
	36		66261138593
	50		66261138592
	60		66261138591
	80		66261138590
9-1/8 x 7/8	24	25	66261138584
	36		66261138583
	50		66261138582

FIBER DISCS MUST ALWAYS BE USED WITH BACK-UP PADS – SEE BELOW

SPEED-CHANGE DISC AVAILABILITY



TIER: **BETTER**
 BRAND: Norton
 TRADENAME: **NORZON BLUEFIRE F826**
 ABRASIVE: Ceramic/Zirconia

SIZE (D X H)	GRIT	STD. PKG.	PART NO.
5 x 5/8-11	24	25	66261138797
	36		66261138796
7 x 5/8-11	24	25	66261138819
	36		66261138818
	50		66261138817
	60		66261138816

SPEED-CHANGE FIBER DISCS MUST ALWAYS BE USED WITH BACK-UP PADS – SEE BELOW



Exceptional Blend of Performance and Price

AVOS DISC AVAILABILITY




TIER: **BETTER**
 BRAND: Norton
 TRADENAME: **NORZON BLUEFIRE F826**
 ABRASIVE: Ceramic/Zirconia

SIZE	GRIT	STD. PKG.	PART NO.
4-1/2"	24	10	66261129718
Speed-Lok (3 hole)	36		66261129719
	50		66261129720
	60		66261129721
	80		66261129722
5" Speed-Lok (3 hole)	24	10	66261126556
	36		66261126557
	50		66261126558
	60		66261126559
7" Speed-Lok (6 hole)	24	10	66261137454
	36		66261137455
	50		66261137456
	60		66261137457
80		66261137458	

AVOS FIBER DISCS MUST BE USED WITH AVOS BACK-UP PADS – SEE BELOW

BACK-UP PAD AVAILABILITY



DESCRIPTION	MAX. RPM	STD. PKG.	PART NO.
SMOOTH FACE			
5" Medium	12,000	5	63642543235
7" Medium	8,600	5	63642543245



DESCRIPTION	MAX. RPM	STD. PKG.	PART NO.
AIR COOLED STANDARD			
4-1/2" Medium	11,000	5	63642502122
5" Medium	10,000	5	63642543421
7" Medium	8,600	5	63642543422
9" Medium	6,600	5	63642543423

TOOLS			
#103 Retainer Nut	–	10	63642543463
66NS Short Retainer Nut	–	10	63642543461
Spanner Wrench		5	63642543005

RETAINER NUTS ARE NOT INCLUDED WITH BACK-UP PADS. THESE MUST BE ORDERED SEPARATELY.

SEE nortonabrasives.com FOR ADDITIONAL BACKUP PADS

AVOS BACK-UP PAD AVAILABILITY



SIZE	MAX RPM	STD. PKG.	PART NO.
AVOS TRIANGULAR SPEED-LOK BACK-UP PADS			
4-1/2" x 5/8-11	13,000	5	63642502985
5" x 3/8-24 Pistol Grip*	20,000	5	63642503029
5" x 5/8-11	13,000	5	63642502517
5" x 7/16-20 Pistol Grip*	20,000	5	63642503030
AVOS ROUND SPEED-LOK BACK-UP PADS			
7" x 5/8-11 Hard	8,600	5	63642504873
7" x 5/8-11 Medium	8,600	5	63642504874

*USE ON AIR PNEUMATIC AND HIGH-SPEED PISTOL GRIP SANDERS

BETTER

For most abrasive applications, Norton offers up to three product performance levels – GOOD, BETTER and BEST. NorZon BlueFire fiber discs are in the BETTER tier. They represent superior performing products for the user who requires a high level of productivity and low total abrasive cost.

To put Norton abrasives to work for you, call your local Norton distributor or visit our website at www.nortonabrasives.com to view our online catalog and learn about our latest products and applications.



Saint-Gobain Abrasives, Inc.
 PO Box 15008, 1 New Bond Street
 Worcester, MA 01615-0008

www.nortonabrasives.com

U.S. CUSTOMER SERVICE:
 Phone Toll Free: 1 800 551-4413
 Fax Toll Free: 1 800 551-4416
 Local Phone: (254) 918-2313
 Local Fax: (254) 918-2314

CANADA CUSTOMER SERVICE:
 Phone Toll Free: 1 800 263-6565
 Fax Toll Free: 1 800 561-9490



FORM #8267

© Saint-Gobain Abrasives, Inc. March 2011
 AVOS, Norton, and Speed-Lok are registered trademarks and NorZon BlueFire and Speed-Change are trademarks of Saint-Gobain Abrasives, Inc.

