

# 300 Universal Beam Clamp

3000037EG



## Features

- Conforms with Federal Specification WW-H-171 (Type 23), Manufacturers Standardization Society ANSI/MSS-SP-58 (Type 19 and 23), install in accordance with ANSI/MSS-SP-69

## Product Specifications

Part Number	3000037EG
Material	Steel
Finish	Electro-galvanized
Rod Size (RS)	3/8"
Flange Thickness (FT)	13/16" Max
A	1 1/8"
Screw Diameter (Sc)	3/8"
Torque (TQ)	5 ft lb
Static Load 1 (F1)	500 lb
Static Load 2 (F2)	250 lb
Standard Packaging Quantity	100 pc
UPC	78285633976
UNSPSC	31162905
ETIM	EC000464
Approvals	cULus®, FM®

Setscrew must be tightened and torqued onto the sloped side of the I-beam.

Recognizing that torque wrenches are generally not used or available on many job sites, the setscrew should be tightened so it contacts the I-beam and then an additional 1/4 to 1/2 turn added.

