

BC26 Universal Beam Clamp with Tapped Hole

BC260025EG



Features

- One thru-hole for easier installation of threaded rod
- Conforms with Federal Specification WW-H-171 (Type 23), Manufacturers Standardization Society ANSI®/MSS-SP-58 (Type 19 and 23), install in accordance with ANSI/MSS-SP-69

Product Specifications

Part Number	BC260025EG
Material	Steel
Finish	Electro-galvanized
Rod Size (RS)	1/4"
A	15/16"
B	13/16"
Hole Size (HS)	1/4"
Hole Type	Threaded
Screw Diameter (Sc)	1/4"
Torque (TQ)	4 ft lb
Static Load 1 (F1)	100 lb
Static Load 2 (F2)	250 lb
Standard Packaging Quantity	100 pc
UPC	78285634025
UNSPSC	31162905
ETIM	EC000464

Setscrew must be tightened and torqued onto the sloped side of the I-beam.

Recognizing that torque wrenches are generally not used or available on many job sites, the setscrew should be tightened so it contacts the I-beam and then an additional 1/4 to 1/2 turn added.

