


Performance Data

Head	1/3 HP	Shut off 48 ft. / 14.6 m	Feet	10	20	30	40	50	65	70
Flow Rate		Max. Flow 20 gpm / 76 lpm	GPM	20	15	4	1	0	-	-
Head	1/2 HP	Shut off 50 ft. / 15.2 m	Feet	10	20	30	40	50	65	70
Flow Rate		Max. Flow 34 gpm / 129 lpm	GPM	34	29	20	5	0	-	-
Head	3/4 HP	Shut off 62 ft. / 18.9 m	Feet	10	20	30	40	50	65	70
Flow Rate		Max. Flow 52 gpm / 197 lpm	GPM	52	47	38	29	18	-	-
Head	1 HP	Shut off 65 ft. / 19.8 m	Feet	10	20	30	40	50	65	70
Flow Rate		Max. Flow 84 gpm / 318 lpm	GPM	84	77	57	48	24	0	-
Head	1-1/2 HP	Shut off 65 ft. / 19.8 m	Feet	10	20	30	40	50	65	70
Flow Rate		Max. Flow 108 gpm / 409 lpm	GPM	108	100	81	70	44	0	-
Head	2 HP	Shut off 68 ft. / 20.7 m	Feet	10	20	30	40	50	65	70
Flow Rate		Max. Flow 114 gpm / 432 lpm	GPM	114	109	92	85	55	8	-
Head	3 HP	Shut off 81 ft. / 19.8 m	Feet	10	20	30	40	50	65	70
Flow Rate		Max. Flow 144 gpm / 545 lpm	GPM	144	131	116	105	85	50	38



WARNING: Use only with nonflammable liquids compatible with pump component materials and in nonflammable/non-explosive atmospheres.

Call or visit your local branch or go to grainger.com/dayton
for complete product line information



Exclusively from Grainger.