

Calbrite™

Stainless Steel Conduit Systems

Stainless Steel FVCS and FVCD

Features:

- Manufactured in type 316 stainless steel for increased corrosion resistance
- Polished with standard "brite" finish to increase corrosion resistance and aesthetic appearance
- Mounts to all Calbrite stainless steel device boxes
- Lockable cover is ideal for outdoor wiring and high-traffic areas that require durability as well as safety precautions
- Multi-die gasket included
- Approved for use in damp environments



Certifications and Compliances:

Fabricated to UL514A Standards

NEMA 4X approved

NEMA 3R approved for wash-down applications



Applications:

The stainless steel weatherproof box is available in a shallow lid model (S60000FVCS), and a deep lid model (S60000FVCD). Both versions are specially designed for use with single-gang and duplex switch and GFCI requirements. The covers must be mounted vertically and in accordance with all local NEC/AHJ requirements.

Industries Commonly Served:

- Food & Beverage Production & Distribution
- Chemical Plants
- Water & Wastewater Treatment
- Pharmaceuticals & Cosmetics
- Refining & Extraction Sites
- Petrochemical Operations
- Marine & Coastal Facilities
- Pulp and Paper Mills
- Along with other corrosive environments



Size	Part Number	Overall Length	Overall Width	Overall Depth	Cover Depth	Box Depth	Weight (ea) per lb.
3/4"	S60000FVCS	6.000"	3.200"	3.500"	2.000"	1.900"	2.65
3/4"	S60000FVCD	6.000"	3.200"	5.500"	5.000"	1.900"	3.67

*All dimensions are for informational purposes only * Tolerances +/- 5%*