

DAYTON AIR-OPERATED DOUBLE DIAPHRAGM PUMP DATA SHEET 3HJW1, 3HJV8




Technical Specs

	3HJW1	3HJV8
SHIPPING WEIGHT	11.32 LBS	11.3 LBS
MAXIMUM LIQUID TEMPERATURE	180°F (82°C)	212°F (100°C)
INTAKE & DISCHARGE PORTS	1/2" SIDE-PORT NPT	1/2" SIDE-PORT NPT
FLOW	0 - 15 GPM MAX	0 - 15 GPM MAX
MAX AIR SUPPLY PRESSURE	100 PSI (1.4 - 7 KGF/CM ²)	100 PSI (1.4 - 7 KGF/CM ²)
BODY MATERIAL	KYNAR®	KYNAR®
LIFT-DRY, WET	8 FT, 28 FT	8 FT, 28 FT
AIR VALVE		
LUBRICATION	NO LUBRICATION REQUIRED	NO LUBRICATION REQUIRED
MANUAL OVERRIDE	YES	YES
LIQUID SIDE		
EASY REPAIR	YES	YES
FLAT CHECK VALVE	PTFE	PTFE
O-RINGS	PTFE	PTFE
DIAPHRAGMS	SANTOPRENE®	PTFE


DAYTON AIR-OPERATED DOUBLE DIAPHRAGM PUMP

3HJW1, 3HJV8

Dimensional Drawing



Performance Curve



Find it at Grainger.

Call or visit your local branch or go to grainger.com/dayton for complete product line information.

