



## Superstrut<sup>®</sup>

**NEW!**

### Cobra™ One-Piece Cable and Pipe Clamp

#### Takes a bite out of your installation time!

- **One-piece, heavy-duty construction** ready to install right out of the box, no need to break apart and re-assemble, no screws or bolts to drop.
- **Installs quickly and securely** using one hand.
- **Universal bolt head** accepts a range of tools.
- **Eliminates the guesswork** from clamp selection — one catalog number attaches equal trade sizes of EMT and rigid conduit.
- **Parallel hook design** keeps conduits and cable square with strut.
- **Reconfigure wiring without complete disassembly.** Remove cables easily without disturbing neighboring clamps.




Multi-driver combination bolt head accepts a wrench, screwdriver or nut driver.



Attaches a full range of EMT, rigid conduit and cable to strut channels.



Remove cable or pipes easily without disturbing neighboring clamps.



1. Hook clamp into strut channel and hand tighten.



2. Tighten bolt.

## Simple Product Selection, Solid Installation

- **Clear markings on each clamp** identify the catalog number, min./max. outer cable diameters, EMT/Rigid trade sizes, CSA and UL stamps.
- One size clamp works on **equal trade sizes for both EMT and rigid conduit.**
- Works with **all depths of strut** —  $1\frac{3}{16}$ " to  $3\frac{1}{4}$ ".
- **Two hooks on the same side** make the clamp easy to install and keep conduits and cable square with strut.
- **Rugged stirrup and wide saddle design** holds securely with no damage to conduit or cable.
- **Suggested design load** is 200 lbs. ( $\frac{1}{2}$ " to 2"); 350 lbs. ( $2\frac{1}{2}$ " to 4"). Safety factor 4:1 (safety factor = ratio of ultimate load to the design load).
- **Heavy-duty  $\frac{5}{16}$ " hex bolt** with multi-driver head (Robertson square, Phillips cross-recess and slot) provides full range of installation options. Virtually any tool will work!
- **Bright zinc finish** — clamps are electrogalvanized after fabrication for additional durability.



## Ordering Information

Cat. Number	For EMT and Rigid Conduit Trade Size	Cable O.D. Range (in.)	Static Load Limit (lb) Safety Factor = 4	Quantity per Box	UPC Number
<b>Electro Galvanized Steel</b>					
CPC050	$\frac{1}{2}$ "	0.650 - 0.890	200	100	61601310698
CPC075	$\frac{3}{4}$ "	0.860 - 1.110	200	100	61601310700
CPC100	1"	1.100 - 1.400	200	100	61601310702
CPC125	$1\frac{1}{4}$ "	1.400 - 1.725	200	50	61601310704
CPC150	$1\frac{1}{2}$ "	1.690 - 1.980	200	50	61601310706
CPC200	2"	1.980 - 2.576	200	50	61601310708
CPC250	$2\frac{1}{2}$ "	2.576 - 3.060	350	25	61601310710
CPC300	3"	3.060 - 3.626	350	25	61601310712
CPC350	$3\frac{1}{2}$ "	3.626 - 4.126	350	25	61601310714
CPC400	4"	4.126 - 4.626	350	25	61601310716
<b>316 Stainless Steel</b>					
CPC050SS6	$\frac{1}{2}$ "	0.650 - 0.890	200	100	61601310699
CPC075SS6	$\frac{3}{4}$ "	0.860 - 1.110	200	100	61601310701
CPC100SS6	1"	1.100 - 1.400	200	100	61601310703
CPC125SS6	$1\frac{1}{4}$ "	1.400 - 1.725	200	50	61601310705
CPC150SS6	$1\frac{1}{2}$ "	1.690 - 1.980	200	50	61601310707
CPC200SS6	2"	1.980 - 2.576	200	50	61601310709
CPC250SS6	$2\frac{1}{2}$ "	2.576 - 3.060	350	25	61601310711
CPC300SS6	3"	3.060 - 3.626	350	25	61601310713
CPC350SS6	$3\frac{1}{2}$ "	3.626 - 4.126	350	25	61601310715
CPC400SS6	4"	4.126 - 4.626	350	25	61601310717

Stainless steel bolt head is hexagonal and slotted only. Not available in aluminum.

# Thomas & Betts

Please ask your Thomas & Betts sales representative for a complete catalog of quality Thomas & Betts electrical products or visit us at [www.tnb.com](http://www.tnb.com). For customer service, 1-800-816-7809. For technical questions, call 1-888-862-3289.

© 2004 Thomas & Betts Corporation. All rights reserved. Printed in U.S.A. 09/04/10M GM-1235

**Thomas & Betts Corporation**  
Electrical Division  
8155 T&B Boulevard  
Memphis, TN 38125  
901-252-5000

**Thomas & Betts Ltd.**  
700 Thomas Avenue  
Iberville, Québec J2X 2M9  
450-347-5318