




### Performance Data

Head	1/2 HP	Shut off 28 psi / 1.93 bar	PSI	10	15	20	25	30	35	40	45	50
Flow Rate		Max. Flow 32 gpm / 121 lpm	GPM	32	30	28	12	-	-	-	-	-
Head	3/4 HP	Shut off 36 psi / 2.48 bar	PSI	10	15	20	25	30	35	40	45	50
Flow Rate		Max. Flow 35 gpm / 132 lpm	GPM	35	33	26	22	19	1	-	-	-
Head	1 HP	Shut off 44 psi / 3.03 bar	PSI	10	15	20	25	30	35	40	45	50
Flow Rate		Max. Flow 49 gpm / 185 lpm	GPM	49	45	40	34	32	22	13	-	-
Head	1-1/2 HP	Shut off 45 psi / 3.10 bar	PSI	10	15	20	25	30	35	40	45	50
Flow Rate		Max. Flow 57 gpm / 216 lpm	GPM	57	52	46	40	35	26	15	0	-
Head	2 HP	Shut off 51 psi / 3.52 bar	PSI	10	15	20	25	30	35	40	45	50
Flow Rate		Max. Flow 66 gpm / 250 lpm	GPM	66	63	58	55	48	42	34	21	1



**WARNING:** Use only with nonflammable liquids compatible with pump component materials and in nonflammable/non-explosive atmospheres.

Call or visit your local branch or go to [grainger.com/dayton](http://grainger.com/dayton) for complete product line information



Exclusively from Grainger.