

## SANITARY DRUM PUMP 3PXJ9

### TECHNICAL data sheet

#### CENTRIFUGAL DRUM PUMP

Dayton offers several Drum Pump solutions and a broad range of pumps to meet the stringent safety requirements of the sanitary process industry. Sanitary centrifugal pumps offer the ideal solution for transferring juices, concentrates, beer, wine, and cosmetic fragrances from barrels, kettles and Tote® tanks. The pumps incorporate a proven hygienic design and FDA Compliant materials of construction (CFR 21.177) insuring a safe, robust and efficient sanitary solution.

#### APPLICATIONS

- Juices
- Personal Care Products
- Beer
- Concentrates
- Pharmaceuticals
- Wine

TECHNICAL SPECIFICATIONS	
Package	Motor, Pump
Wetted Parts	316 Stainless Steel, PTFE
Pump Length	39" (1000 mm) (Drums)
Maximum Flow Rate	35 GPM (132 LPM) based on water
Maximum Viscosity	1,000 cps (mPAS)
Maximum Temperature	175° F (80° C)
Shipping Weight	22 lbs. (9,97 kg)
Package Number	3PXJ9
Motor	1DLK8
Volts	110v
Pump Tube	3PXJ9

