

DYMO

Datacom and Facility

Rhino® 5200

Advanced Labeling Tool



Outperforms industrial labelers costing twice as much.

Leave any jobsite looking better than you found it.

Rugged, versatile and packed with time-saving features, the DYMO Rhino™ 5200 meets all ANSI and TIA/EIA-606-A labeling standards. Time is money, and exclusive one-touch “Hot Keys” save you both on every job. Just press one “Hot Key” to automatically size, space and format text for perfect patch panel labels – then press another to print matching cable flags or face plate tabs, without retyping!

It's just as easy to print module and fixed-length labels, horizontal and vertical wire wraps, terminal and 110 blocks and much more. Print Code 39 and Code 128 barcodes. Access 100+ industry symbols, fractions and punctuation marks with a few quick keystrokes. Add the optional quick-charging lithium-ion battery for uninterrupted productivity.



Hard Case Kit
(see back for details)



DYMO® | Rhino 5200 features:

- 1 Meets all ANSI and TIA/EIA-606-A industry labeling standards
- 2 Exclusive one-touch “Hot Keys” automatically size, space and format label text for electrical and patch panels, terminal and 110 blocks, wire and cable flags, horizontal and vertical wraps, vertical and fixed-length applications
- 3 Prints Code 39 and Code 128 barcodes on 3/4" (19 mm)-wide labels – ideal for asset management
- 4 Uses DYMO Industrial labels with chemical-, heat- and UV-resistant materials; also prints directly on heat-shrink tubes and non-adhesive labels
- 5 Large 14-character, two-line backlit display
- 6 100-Label Memory for storing commonly used labels



Up to

