

14000 Dynafile

14010 Dynafile Versatility Kit

- World-famous Dynafile replaces tedious hand filing and sanding. Grind, deburr, blend, polish, finish and more!
- Grind from contact wheel or platen pad. Finish and polish using slack of belt. For use on metal, plastic, fiberglass, composites, rubber, glass and stone.
- Tool includes 11218 Contact Arm for standard use. Also accepts a variety of additional Contact Arms. Superior belt tracking permits use of abrasive belts 1/8", 1/4" or 1/2" wide x 24" long. Work in areas as small as 3/8" diameter.
- Motor easily adjusts to the most comfortable throttle lever position. Lightweight composite belt guard allows quick and easy belt change!
- Hard and soft platen pads mount onto Contact Arms for heavy grinding or contour polishing.
- 14010 Versatility Kit includes tool with popular contact arms and an assortment of abrasive belts in a durable case.

14000, 14010

Dynafile Abrasive Belt Tool

.5 hp, Straight-Line, 20,000 RPM, Front Exhaust, for 1/8"-1/2" W x 24" L (3-13 mm x 610 mm) Belts

Belt Size Inches (mm): 1/8-1/2" (3-13) W x 24" (610) L

hp (W): .5 (373)

Motor Free Speed (RPM): 20,000

Max. SFPM (SM/Min.): 5,800 (1,762)

Motor Style: Straight-Line

Exhaust Type: Front Exhaust

Max. Air Flow @ 90 PSIG (6.2 Bar): 31 (878)
SCFM (L/Min.):

Air Inlet Thread:	1/4" NPT
Hose I.D. Size Inches (mm):	1/4" (6)
Length Inches (mm):	14.6" (371)
Height Inches (mm):	4.6" (116)
Sound Level dB(A):	77
Vibration Tool Peak Axis ISO8662 (m/sec ²):	<2.5
Item Weight:	3.32 lbs