

.4 hp Die Grinder

Ergo-Grip, Right Angle

Safety, Operation and Maintenance – Save This Document and Educate All Personnel

Model	RPM	Exhaust	Muffler	Insert Size
46000	12,000	Rear	Extended	1/4" & 6 mm
46001	15,000	Rear	Extended	1/4" & 6 mm
46002	20,000	Rear	Extended	1/4" & 6 mm
47800	12,000	Front	Front	1/4" & 6 mm
47801	15,000	Front	Front	1/4" & 6 mm
47802	20,000	Front	Front	1/4" & 6 mm
48315	12,000	Rear	Standard	1/4" & 6 mm
48316	15,000	Rear	Standard	1/4" & 6 mm
48317	20,000	Rear	Standard	1/4" & 6 mm
49425	3,200	Rear	Standard	1/4" & 6 mm



Model 46002



Find The Most Current Offering of Support Documents and Accessories at www.Dynabrade.com

⚠ WARNING

Read and understand this tool manual before operating your air tool. Follow all safety rules for the protection of operating personnel as well as adjacent areas. Always operate, inspect and maintain this tool in accordance with the American National Standards Institute (ANSI) Safety Code for Portable Air Tools – B186.1. For additional safety information, refer to Safety Requirements for the Use, Care and Protection of Abrasive Wheels – ANSI B7.1, Code of Federal Regulation – CFR 29 Part 1910, European Committee for Standards (EN) Hand Held Non-Electric Power Tools – Safety Requirements and applicable State and Local Regulations.



Read and understand tool manual before work starts to reduce risk of injury to operator, visitors, and tool.



Eye protection must be worn at all times, eye protection to conform to ANSI Z87.1.



Ear protection to be worn when exposure to sound, exceeds the limits of applicable Federal, State or local statutes, ordinances and/or regulations.



Practice safety requirements. Work alert, have proper attire, and do not operate tools under the influence of alcohol or drugs.



Respiratory protection to be used when exposed to contaminants that exceed the applicable threshold limit values required by law.



Air line hazard, pressurized supply lines and flexible hoses can cause serious injury. Do not use damaged, frayed or deteriorated air hoses and fittings.

Some dust created by sanding, grinding, drilling, and other construction activities contain chemicals known to cause cancer, birth defects or other reproductive harm. Some examples of these chemicals are:

- Lead from lead-based paints
- Crystalline silica from bricks and cement and other masonry products
- Arsenic and chromium from chemically treated lumber

Your risk from these exposures varies, depending on how often you do this type of work. To reduce your exposure to these chemicals: work in a well ventilated area, and work with approved safety equipment, such as those dust masks that are specially designed to filter out microscopic particles.

SAFETY INSTRUCTIONS



Carefully Read and Understand the General and Die Grinder sections found in Tool Safety and Operating Guidelines (PN00001676) Before Handling or Using Tool.

Carefully Read all instructions before operating or servicing any Dynabrade® Abrasive Power Tool. Products offered by Dynabrade are not to be modified, converted or otherwise altered from the original design.

Tool Intent: .4 hp Die Grinder is ideal for deburring, deflashing, surface preparation, cleaning and finishing using proper abrasive stones, abrasive mounted wheels, molded abrasives and carbide burrs. Intended for use with abrasives less than 2" (50 mm) diameter.

DO NOT USE Tool for Anything Other Than Its Intended Applications.

Training: Proper care, maintenance, and storage of your air tool will maximize tools performance and reduce chance for accident.

Employer's Responsibility: Provide operators with safety instructions and training for safe use of tools and accessories.

Report to Your Supervisor any Condition of the Tool, Accessories or Operation you Consider Unsafe.

MAINTENANCE INSTRUCTIONS

Important: To keep tool safe, a Preventative Maintenance Program is recommended. The program should include inspection of the tool and all related accessories and consumables, including air lines, pressure regulators, filters, oilers, etc. refer to ANSI B186.1 for additional maintenance information. If accessory or tool breakage occurs, investigate failure to determine the cause and correct before issuing tool for work. Use the following schedule as a starting point in developing a Preventative Maintenance Program. If tool does not operate properly (RPM, Vibration, Start/Stop) after these scheduled checks or at any time, the tool must be repaired and corrected before returning tool to use.

INSTALLATION

- To ensure long life and dependable service, use a Closed Loop Air System and Filter-Regulator-Lubricator as diagrammed below.
- Each tool should have its own dedicated hose connected to an air supply manifold. Quick disconnects should be installed at the manifold in an effort to reduce contamination into the tool.
- It is strongly recommended that all Dynabrade rotary vane air tools be used with a Filter-Regulator-Lubricator to minimize the possibility of misuse due to unclean air, wet air or insufficient lubrication. Dynabrade recommends the following: **10681** Air Line Filter-Regulator-Lubricator — Provides accurate air pressure regulation, two-stage filtration of water contaminants and micro-mist lubrication of pneumatic components.
- Dynabrade recommends one drop of air lube per minute for each 20 SCFM (example: if the tool specification states 40 SCFM, set the drip rate on the filter-lubricator to 2 drops per minute) Dynabrade Air Lube (P/N **95842**: 1pt/473ml) is recommended.

MAINTENANCE SCHEDULE

Daily (every 8 hours):

- Inspect tool and accessories for damage or broken parts. Replace items as necessary to ensure proper operation and safety.
- Lubricate motor as recommended. Use Dynabrade Air Lube (P/N **95842**: 1pt/473ml) 10W/NR. (1 Drop per minute of air lube per 20 SCFM.)
- Check air line pressure with a gage. (MAX. 90 PSIG or 6.2 Bar operating pressure at the air inlet of the tool.)
- Right angled gear and wick system through gear case grease fitting with 3 plunges of gear oil (P/N **95848**) and grease gun (P/N **95541**). (Prime grease gun prior to greasing.)
- Check tool for proper operation: If operating improperly or demonstrates unusual vibration, the tool must be serviced and problem corrected before further use.

Every 20 Hours or Once a Week Which Ever Comes First:

- Check free speed of tool without the abrasive accessory mounted. Measure RPM (speed) with tachometer and with air pressure set at 90 PSIG while the tool is running. If a governed tool is operating at a higher speed than the RPM marked on the tool housing, the tool must be serviced and corrected before use. A non-governed tool may exceed the RPM marked on the tool by 10% when operated at free speed with no accessories.
- If tool is running fast look for worn, damaged or missing governors, air control rings and silencers. Special care must be taken when servicing

governors and speed control devices. Injection molded governor assemblies are non-serviceable and must be replaced.

- If tool is running slow look for clogged inlet screen, air stream, silencer(s) or a malfunctioning governor (see concerns for servicing governors). Service as required.

Every 50 Hours:

- Lubricate planetary gears through gear case grease fitting with 3 plunges of grease (P/N **95542**) and grease gun (P/N **95541**). (Prime grease gun prior to greasing.)

REPAIR

- Use only genuine Dynabrade replacement parts to ensure quality. To order replacement parts, specify Model#, Serial# and RPM of your air tool.
- Mineral spirits are recommended when cleaning the tool and parts. Do not clean tool or parts with any solvents or oils containing acids, esters, ketones, chlorinated hydrocarbons or nitro carbons.
- DO NOT clean or maintain tools with chemicals that have a low flash point (example: WD-40®).
- Motor Tune-Up Kit are available (when applicable) which includes high wear and medium wear motor parts.
- Air tool markings must be kept legible at all times, if not, reorder housing and replace. User is responsible for maintaining specification information.
- After maintenance is performed on tool, add a few drops of Dynabrade Air Lube (P/N **95842**) to the tool inlet and start the tool a few times to lubricate air motor. Verify RPM (per 20 hr maintenance schedule), vibration and operation.

HANDLING & STORAGE

- Use of tool rests, hangers and/or balancers is recommended.
- Protect tool inlet from debris (see Notice).
- DO NOT carry tool by air hose or near the tool throttle lever.
- Store accessories in protective racks or compartments to prevent damage.
- Follow the handling instructions outlined in the operating instructions when carrying the tool and when changing accessories.
- Protect accessories from exposure to water, solvents, high humidity, freezing temperature and extreme temperature changes.

END OF USE/DISPOSAL



When tool has reached its end of useful service, disassemble tool into its primary components (i.e. steel, aluminum and plastic part) and recycle or discard per local, state and/or federal regulations as to not harm the environment.

NOTICE

All Dynabrade motors use the highest quality parts and metals available and are machined to exacting tolerances. The failure of quality pneumatic motors can most often be traced to an unclean air supply or the lack of lubrication. Air pressure easily forces dirt or water contained in the air supply into motor bearings causing early failure. It often scores the cylinder walls and the rotor blades resulting in limited efficiency and power. Our warranty obligation is contingent upon proper use of our tools and cannot apply to equipment which has been subjected to misuse such as unclean air, wet air or a lack of lubrication during the use of this tool.

AIR SYSTEM

Closed Loop Pipe System, Sloped in Direction of Air Flow



- Dynabrade Air Power Tools are designed to operate at 90 PSIG (6.2 Bar) maximum air pressure at the tool inlet, when the tool is running. Use recommended regulator to control air pressure.
- Ideally the air supply should be free from moisture. To facilitate removing moisture from air supply, the installation of a refrigerated air dryer after the compressor and the use of drain valves at each tool station is recommended.


Models

**46000, 46001, 46002, 47800,
47801, 47802, 48315, 48316,
48317, 49425**

.4 hp Die Grinder Complete Assembly

Index Key

No.	Part #	Description
1	01484	Collet Cap
2	01485	Collet Insert
	1/4"	
3	01497	6 mm
4	02035	Lock Nut
5	02032	Collet Body - Spindle
6	01486	Felt Silencer (5 - Rear Exht.)
7	54520	Bearing (2 - Mdl: 49425)
8	97116	Shim .001" (As Required)
9	97117	Shim .002" (As Required)
10	97118	Shim .005" (As Required)
10	Gear	
11	02623	12,000 RPM
	02597	15,000 RPM
	02599	3,200 & 20,000 RPM
11	Wick - Bottom	
12	02042	12,000 RPM
	02044	3,200, 15K, 20K RPM
12	Wick - Top	
13	02043	12,000 RPM
	02045	3,200, 15K, 20K RPM
13	02033	Needle Bearing
14	02041	Gear Oil Plate
15	01041	Lube Fitting (2 - Mdl: 49425)
16	Right Angle Housing	
17	02052	Front Exhaust Models
	02031	Rear Exhaust Models
17	01728	Felt Silencer (Front Exhaust)
18	Pinion	
19	02624	12,000 RPM
	02598	15,000 RPM
	02600	3,200 & 20,000 RPM
19	50019	Lock Nut
20	02649	Bearing
21	50022	Spacer
22	50023	Planetary Carrier
23	06213	Gear (2)
24	54472	Pin (2)
25	54468	Ring Gear
26	50024	Gear Case
27	50784	Set Screw
28	54543	Shim -.001" (As Required)
29	54544	Shim -.002" (As Required)
30	54551	Shim -.003" (As Required)
31	01478	Front Bearing Plate
32	50767	Pin (2)
33	01479	Spacer
34	01480	Vane Set (4/Pkg.)
35	Rotor	
35	45291	3,200 RPM
	45293	12K, 15K, 20K RPM
36	01476	Cylinder
37	02676	Rear Bearing Plate
38	02696	Bearing
39	96077	O-Ring
40	Governor Assembly	
41	45269	3,200 RPM (Blue)
	45272	12K, 15K, 20K RPM (Green)
41	45320	Governor Chamber
42	45305	Housing Core (Mdl: 49425)
	45307	Housing Core (12,000 RPM & higher)
43	01547	Collar
44	45315	Throttle Bushing
45	97045	Pin
46	45263	Safety Throttle Lever
47	97060	Pin
48	Exterior Housing (Laser Etched)	
48	45211	Model - 46000
	45212	Model - 46001
	45213	Model - 46002
	45214	Model - 47800
	45215	Model - 47801
	45216	Model - 47802
	45224	Model - 48315
	45225	Model - 48316
	45226	Model - 48317
	45230	Model - 49425
49	45310	Seal
50	58365	Tip Valve
51	01468	Spring
52	01564	Air Control Ring
53	53190	Block Plate
54	96065	O-Ring
55	01494	Inlet Adapter Assembly
56	95711	Retaining Ring
57	01446	Air Deflector
58	95620	Retaining Ring
59	01578	Inlet Adapter Assembly
60	95438	O-Ring
61	94521	Muffler Base
62	94524	Sintered Bronze Muffler
63	94525	Felt Muffler
64	94522	Muffler Cap
65	95375	O-Ring
66	94526	Spacer
67	94523	Inlet Adapter Assembly
68	94535	Standard Muffler Assembly
69	94520	Extended Muffler Assembly



95262 14 mm Wrench

See
Page 4
for
Overhose
Assemblies

LIFETIME WARRANTY

To validate Dynabrade Lifetime Warranty, you must register each tool at: www.dynabrade.com. Registration of each tool at website is required. Dynabrade will not honor Lifetime Warranty on unregistered tools. Please view the entire Lifetime Warranty Policy at : www.dynabrade.com.



MACHINE SPECIFICATIONS

Model	Speed	Power	Sound	Air Consumption	Collet Size	Weight	Length	Height
46000	12,000 RPM	.4 hp (298 W)	78 db(A)	23 SCFM 651 (LPM)	1/4" & 6 mm	1.2 lb. (.55 kg)	8" (203 mm)	2.9" (73 mm)
46001	15,000 RPM	.4 hp (298 W)	75 db(A)	23 SCFM 651 (LPM)	1/4" & 6 mm	1.2 lb. (.55 kg)	8" (203 mm)	2.9" (73 mm)
46002	20,000 RPM	.4 hp (298 W)	78 db(A)	23 SCFM 651 (LPM)	1/4" & 6 mm	1.2 lb. (.55 kg)	8" (203 mm)	2.9" (73 mm)
47800	12,000 RPM	.4 hp (298 W)	84 db(A)	25 SCFM 708 (LPM)	1/4" & 6 mm	1 lb. (.46 kg)	6" (150 mm)	2.9" (73 mm)
47801	15,000 RPM	.4 hp (298 W)	86 db(A)	25 SCFM 708 (LPM)	1/4" & 6 mm	1 lb. (.46 kg)	6" (150 mm)	2.9" (73 mm)
47802	20,000 RPM	.4 hp (298 W)	85 db(A)	25 SCFM 708 (LPM)	1/4" & 6 mm	1 lb. (.46 kg)	6" (150 mm)	2.9" (73 mm)
48315	12,000 RPM	.4 hp (298 W)	81 db(A)	23 SCFM 651 (LPM)	1/4" & 6 mm	1 lb. (.47 kg)	6.5" (164 mm)	2.9" (73 mm)
48316	15,000 RPM	.4 hp (298 W)	79 db(A)	23 SCFM 651 (LPM)	1/4" & 6 mm	1 lb. (.47 kg)	6.5" (164 mm)	2.9" (73 mm)
48317	20,000 RPM	.4 hp (298 W)	83 db(A)	23 SCFM 651 (LPM)	1/4" & 6 mm	1 lb. (.47 kg)	6.5" (164 mm)	2.9" (73 mm)
49425	3,200 RPM	.4 hp (298 W)	81 db(A)	23 SCFM 651 (LPM)	1/4" & 6 mm	1.5 lb. (.68 kg)	7.7" (196 mm)	2.9" (73 mm)

Additional Specifications: Air Inlet Thread 1/4" NPT • Hose I.D. 1/4" (6 mm)

Sound Level is the pressure measurement according to the method outlined in ISO regulation ISO-15744

OPTIONAL ACCESSORIES



- Motor Tune-Up Kit**
- Includes assorted parts to help maintain and repair motor.
- Part No. 96541



Dynabrade Air Lube

- Formulated for pneumatic equipment.
- Absorbs up to 10% of its weight in water.
- Prevents rust and formation of sludge.
- Keeps pneumatic tools operating longer with greater power and less down time.

Part No. 5842: 1pt. (473 ml)
Part No. 5843: 1gal. (3.8 L)



Overhose Assembly

- Redirects exhaust away from operator.


Part No. 94994

- For use with standard exhaust models only.

Part No. 94995

- For use with extended exhaust models only.

SPECIAL REPAIR TOOLS



Hex Key Wrench

- 12 mm hex
- Use in housing core or air inlet.


Part No. 96399



Crowfoot Wrench

- 3/8" Drive
- 34 mm
- Use on throttle body, housing core and lock nuts.

Part No. 96460



Repair Collar

- Used to protect right angle and 7° offset housings when placed in a vise.

Part No. 96461

REFERENCE CONTACT INFORMATION

- American National Standards Institute – ANSI**
1899 L Street, NW
11th Floor
Washington, DC 20036
Tel: 1 (212) 642-4900
- Government Printing Office – GPO**
Superintendent of Documents
Attn. New Orders
P.O. Box 371954
Pittsburgh, PA 15250-7954
Tel: 1 (202) 512-1803
- Power Tool Institute, Inc.**
P.O. Box 818
Yachata, Oregon 97498-0818
Tel: 1 (503) 547-3185
- European Committee for Standardization**
Rue de Stassart 36
B - 1050 Brussels, Belgium

DYNABRADE, INC.

8989 Sheridan Drive • Clarence, NY 14031-1419 • Phone: (716) 631-0100 • Fax: 716-631-2073 • International Fax: 716-631-2524
©DYNABRADE, INC., 2012

PRINTED IN USA

www.dynabrade.com

PD12.04_02/12

