

# .5 hp Die Grinders

## Straight-Line, Gearless, Front Exhaust



**COLLET INSERTS**  
PAGE 51

**COUPLER/PLUG**  
PAGE 228

**DYNASWIVEL®**  
PAGE 223

**ACCESSORIES**  
PAGE 222

### High-Quality Air-Powered Die Grinders

- Gearless for reduced maintenance and downtime.

FOR USE WITH  
Carbide Burrs, Rotary Files,  
Mounted Points and Discs  
SEE PAGE 251

#### Model 51300

15,000 RPM, 1/4" & 6 mm Collets

#### Model 51301

18,000 RPM, 1/4" & 6 mm Collets

#### Model 51302

20,000 RPM, 1/4" & 6 mm Collets

#### Model 51303

24,000 RPM, 1/4" & 6 mm Collets



Model 51301



Model Number	Motor hp (W)	Motor RPM	Sound Level	Maximum Air Flow SCFM (L/Min)	Hose I.D. Size Inch (mm)	Air Inlet Thread	Tool Thread	Weight Pound (kg)	Length Inch (mm)	Height Inch (mm)
51300	.5 (373)	15,000	78 dB(A)	24 (680)	3/8 (10)	1/4" NPT	3/8"-24 Male	1.5 (0.7)	7 (178)	1-7/8 (48)
51301	.5 (373)	18,000	78 dB(A)	24 (680)	3/8 (10)	1/4" NPT	3/8"-24 Male	1.5 (0.7)	7 (178)	1-7/8 (48)
51302	.5 (373)	20,000	80 dB(A)	25 (708)	3/8 (10)	1/4" NPT	3/8"-24 Male	1.5 (0.7)	7 (178)	1-7/8 (48)
51303	.5 (373)	14,000	83 dB(A)	26 (736)	3/8 (10)	1/4" NPT	3/8"-24 Male	1.5 (0.7)	7 (178)	1-7/8 (48)

Tune-Up Kit: No. 95600 (page 267) • Additional Specifications: Air Pressure 90 PSIG (6.2 Bar)

# .5 hp Die Grinders

## Straight-Line, Gearless, Rear Exhaust



**COLLET INSERTS**  
PAGE 51

**DYNAJET**  
PAGE 224

**COUPLER/PLUG**  
PAGE 228

**ACCESSORIES**  
PAGE 222

### High-Quality Air-Powered Die Grinders

- Gearless for reduced maintenance and downtime.
- Extended rear exhaust muffler design ensures lowest sound level.

FOR USE WITH  
Carbide Burrs, Rotary Files,  
Mounted Points and Discs  
SEE PAGE 251

#### Model 51304

15,000 RPM, 1/4" & 6 mm Collets

#### Model 51305

18,000 RPM, 1/4" & 6 mm Collets

#### Model 51306

20,000 RPM, 1/4" & 6 mm Collets

#### Model 51307

24,000 RPM, 1/4" & 6 mm Collets



Model 51304



Model Number	Motor hp (W)	Motor RPM	Sound Level	Maximum Air Flow SCFM (L/Min)	Hose I.D. Size Inch (mm)	Air Inlet Thread	Tool Thread	Weight Pound (kg)	Length Inch (mm)	Height Inch (mm)
51304	.5 (373)	15,000	76 dB(A)	25 (708)	3/8 (10)	1/4" NPT	3/8"-24 Male	1.8 (0.8)	9-1/4 (235)	1-7/8 (48)
51305	.5 (373)	18,000	74 dB(A)	26 (736)	3/8 (10)	1/4" NPT	3/8"-24 Male	1.8 (0.8)	9-1/4 (235)	1-7/8 (48)
51306	.5 (373)	20,000	75 dB(A)	27 (765)	3/8 (10)	1/4" NPT	3/8"-24 Male	1.8 (0.8)	9-1/4 (235)	1-7/8 (48)
51307	.5 (373)	14,000	76 dB(A)	27 (765)	3/8 (10)	1/4" NPT	3/8"-24 Male	1.8 (0.8)	9-1/4 (235)	1-7/8 (48)

Tune-Up Kit: No. 96530 (page 267) • Additional Specifications: Air Pressure 90 PSIG (6.2 Bar)

DIE GRINDERS