

DID YOU KNOW?

The proper handling and disposal of construction and project waste is an important part of pollution prevention.

HAZARD HUT®

THE SOLUTION TO YOUR INDOOR STORAGE PROBLEM IS OUTDOOR CONTAINMENT.

ENHANCED DESIGN!

When floor space is unavailable indoors, take your hazardous materials outdoors with Hazard Hut®. One-piece molded 100% polyethylene construction allows for no joints or seams to leak. Molded-in side vents reduce fumes, while UV protection makes it a durable performer outside. Removable grates make it easy to clean the 72-gallon sump capacity and ensures leak and spill containment.


The newly-enhanced double doors provide added security and strength. Easy access for up to four (4) 55-gallon drums is provided while the double-wall and newly-enhanced hinges and lock latches keep contents secure. Hazard Hut® has a heavy-duty, four-way forkliftable design.



Door opening 41.5" W x 48.5" H



Massive sump has removable grates for easy cleaning.



Enhanced doors and lock for added security.

HAZARD HUT®

Part #	Description	Int. Dimension in. (cm)	Ext. Dimension in. (cm)	Weight lb. (kg)	Spill Cap. gal. (L)	Load Cap. lb. (kg)
4000-YE		53.75 x 53.75 x 52.25 (137 x 137 x 133)	63.5 x 68 x 72.5 (161 x 173 x 184)	268.7 (121.8)	72 (275.5)	4,000 (1,814)

Regulations: EPA 40 CFR 264.175, SPCC, NPDES and UFC



HAZARD HUT® POLY-RAMP

Loading the Hazard Hut® is easy with our Hazard Hut® Poly-Ramp. Just roll up the ramp and roll on the barrels!

Hazard Hut® Poly-Ramp features:

- Integrally molded handles
- 10° slope allows for easy loading
- Improved ribbed, non-skid surface
- 100% polyethylene

HAZARD HUT® POLY-RAMP

Part #	Dimensions in. (cm)	Weight lb. (kg)	Load Cap. lb. (kg)
4001-BK	118 x 31 x 15.25 (300 x 79 x 39)	154.1 (69.9)	1,000 (454)