

2 & 4-DRUM HARDCOVER™ & SPILLPALLETS

ENPAC Hardcovers are a sturdy, ideal solution for indoor & outdoor storage of up to four (4) 55-gallon drums. Available in a 2 and 4 drum unit, these uniquely engineered, roll-top cover designed Spillpallets allow for ample use in limited space or next to buildings where swing-open doors would be a problem. Extended vertical space allows for continued use of drum pumps and funnels while removable grates provide access to the spill sump for easy cleaning. The Hardcover Spillpallet units are completely weatherproof and feature a newly-enhanced lockable door! Also available in ECO-Efficient and with optional ramp, ramp extender and drain. Some assembly required.

Features Include:

- Award-winning and best-selling ENPAC Spillpallet Base (5253-YE, 5400-YE)
- Removable grates for easy cleaning
- Lockable Door for added security
- Weatherproof for the harshest conditions
- Optimal height for drum dispensing advantage
- Ships unassembled to save on freight

Options:

- Drain
- Ramp (See page 9)
- Ramp Extender (2-Drum Unit) (See page 9)



**ENHANCED
LOCK &
DOOR!**



2 & 4-DRUM HARDCOVER™ & SPILLPALLET

Part #	Description	Ext. Dimensions L x W x H in. (cm)	Int. Dimension in. (cm)	Weight lb. (kg)	Spill Cap. gal. (L)	Load Cap. lb. (kg)
4062-YE 4062-YE-D	2-Drum (w/drain)	60 x 37.25 x 72.63 (152 x 95 x 184)	51 x 30 x 52 (130 x 76 x 132)	210 (95)	58 (220)	2,000 (907)
4064-YE 4064-YE-D	4-Drum (w/drain)	65 x 58 x 69 (165 x 147 x 175)	49 x 54 x 53.5 (124 x 137 x 136)	269 (122)	66 (250)	6,000 (2,722)

Regulations: EPA 40 CFR 264.175, SPCC, NPDES and UFC

CROSS-CONTAIN™ POLY-SPILLPALLETS

DEFINING SHIPPING AND STORAGE EFFICIENCY

The Cross-Contain™ Poly-Spillpallets offer the lowest platform, highest containment structure available for up to 4-drums. Dynamic low profile designs allow for easy dispensing, filling and pumping.

The open sump grate configurations promote easy inspection and direct access to spills without needing to move the drums. Placing weight on the internal platform and not the sump walls allows the units to store up to 6,000 lb with a spill capacity of up to 85 gallons. Maintain productivity while satisfying government regulations with these compact and economical units!

- 2-Drum** - Low profile design keeps drums 6" off the floor for efficient access and use of drums.
- 4-Drum** - Transport pallets become 'removable platforms' and help to reduce drum and product handling. Can be used with or without a transport pallet.

* Grates come in standard black



NEW!



SuperShipper™



CROSS-CONTAIN™ POLY-SPILLPALLET

Part #	Description	Ext. Dimension L x W x H in. (cm)	Weight lb. (kg)	Spill Cap. gal. (L)	Load Cap. lb. (kg)
5393-BK	2-Drum	58 x 34.5 x 12 (147 x 88 x 31)	44 (20)	75 (284)	6,000 (2,721)
5394-BK	4-Drum Deluxe	56 x 56 x 10 (142 x 142 x 25)	74 (10.8)	85 (322)	6,000 (2,721)

Regulations: 40 CFR 264.175, SPCC, NPDES and UFC