



# STINGER SNAP-UP BERM™

**THE WORLDWIDE LEADER IN LARGE, AGGRESSIVE AND IMMEDIATE SPILL RESPONSE.**

The ENPAC® Stinger Berm™ leads the industry with its wide range of sizes and capacities for large-scale spill containment. Stinger Berms feature excellent rip, tear, and puncture resistance for the most demanding application or terrain. Ground Pad and TracMat™ provide additional protection.



**NEW SIZES!**

- Easy to assemble snap-up design permits immediate response
- Compact storage and transport
- Air-lance tested containment welds for maximum product performance
- Lap joint welds for maximum strength
- Individual serial numbers
- CAD designed and cut components
- Fuel/chemical resistant containment area
- Custom sizes and special materials available
- Cold rated to -30° F/-34° C
- Available in Arctic Grade
- Now available in a 2' L-Bracket sidewall!



Easy set up and take down.  
Custom sizes and special materials available.



## STINGER SNAP-UP BERMS™

Part #	Dimensions L x W x H ft. (m)	Weight lb. (kg)	Spill Cap. gal. (L)
4801-BK-SU	4 x 4 x 8" (1.2 x 1.2 x 20 cm)	11 (5)	80 (302)
4802-BK-SU	4 x 4 x 1 (1.2 x 1.2 x 30 cm)	18 (11.4)	119 (451)
4803-BK-SU	4 x 6 x 8" (1.2 x 1.8 x 20 cm)	25 (8)	119 (451)
4804-BK-SU	4 x 6 x 1 (1.2 x 1.8 x 30 cm)	28 (13)	179 (678)
4805-BK-SU	4 x 8 x 8" (1.2 x 2.4 x 20 cm)	21 (9.5)	159 (602)
48-5101-BK-SU	5 x 10 x 1 (1.5 x 3 x 30 cm)	45 (20)	374 (1,416)
4806-BK-SU	6 x 6 x 1 (1.8 x 1.8 x 30 cm)	37 (16.3)	269 (1,018)
4807-BK-SU	8 x 8 x 8" (2.4 x 2.4 x 20 cm)	35 (16)	319 (1,207)
4810-BK-SU	10 x 10 x 1 (3.1 x 3.1 x 30 cm)	60 (27.3)	748 (2,831)
4812-BK-SU	12 x 12 x 1 (3.7 x 3.7 x 30 cm)	80 (36.3)	1,077 (4,077)
4816-BK-SU	16 x 16 x 1 (4.9 x 4.9 x 30 cm)	113 (51)	1,914 (7,245)
4820-BK-SU	10 x 26 x 1 (3.1 x 7.9 x 30 cm)	122 (55)	1,944 (7,359)
48-10401-BK-SU	10 x 40 x 1 (3 x 12.2 x 30 cm)	150 (68)	2,992 (11,326)
48-10451-BK-SU	10 x 45 x 1 (3 x 13.7 x 30 cm)	155 (70)	3,366 (12,742)
48-12201-BK-SU	12 x 20 x 1 (3.7 x 6 x 30 cm)	130 (58)	1,795 (6,795)
4826-BK-SU	12 X 26 X 1 (3.7 X 7.9 X 30 cm)	140 (63)	2,334 (8,835)
4836-BK-SU	12 x 36 x 1 (3.7 x 11 x 30 cm)	165 (74.8)	3,231 (12,230)
48-12501-BK-SU	12 x 50 x 1 (3.7 x 15.2 x 30 cm)	250 (113)	4,488 (16,989)
4850-BK-SU	15 x 50 x 1 (4.6 x 15.2 x 30 cm)	268 (121)	5,610 (21,236)
4854-BK-SU	14 x 54 x 1 (4.3 x 16.5 x 30 cm)	252 (114.5)	5,654 (21,402)
4860-BK-SU	12 x 60 x 1 (3.7 x 18.3 x 30 cm)	285 (129)	5,385 (20,384)
4866-BK-SU	14 x 66 x 1 (4.3 x 20.1 x 30 cm)	337 (153)	6,911 (26,160)
4885-BK-SU	14 x 85 x 1 (4.3 x 25.9 x 30 cm)	500 (227)	8,901 (33,693)
48-20401-BK-SU	20 x 40 x 1 (6 x 12.2 x 30 cm)	280 (127)	5,984 (22,652)
48-20601-BK-SU	20 x 60 x 1 (6 x 18.3 x 30 cm)	600 (272)	8,976 (33,979)
48-25401-BK-SU	25 x 40 x 1 (7.6 x 12.2 x 30 cm)	310 (140)	7,480 (28,314)

Regulations: EPA 40 CFR 264.175, SPCC, NPDES

## STINGER L-BRACKET BERMS™

Part #	Dimensions L x W x H ft. (m)	Weight lb. (kg)	Spill Cap. gal. (L)
48-10102-SU-SS	10 x 10 x 2 (3 x 3 x 61 cm)	180 (81)	1,496 (5,663)
48-15152-SU-SS	15 x 15 x 2 (4.6 x 4.6 x 61 cm)	220 (99)	3,366 (12,742)
48-20202-SU-SS	20 x 20 x 2 (6.1 x 6.1 x 61 cm)	380 (172)	5,984 (22,652)

Regulations: EPA 40 CFR 264.175, SPCC, NPDES

\*Image not shown.