



**FEATURES**

**Impeller:** Cast iron, ASTM A48, Class 30, two vane semi-open, non-clog design with pump out vanes for mechanical seal protection. Balanced for smooth operation. Silicon bronze impeller is an option.

**Casing:** Heavy duty gray cast iron, ASTM A48, Class 30. Volute type casing with 3", 125#, ANSI flanged, horizontal discharge. Compatible with A10-30 cast iron or A10-30B cast iron and brass (non-sparking) guide rail assembly.

**Dual Mechanical Seals:** Silicon carbide vs. silicon carbide outer seal and ceramic vs. carbon inner seal, stainless steel metal parts, BUNA-N elastomers. Upper and lower shaft seals are positioned independently and are separated by an oil-filled chamber.

**Shaft:** 300 series stainless steel keyed design.

**Fasteners:** 300 series stainless steel.

Capable of running dry temporarily without damage to seals or motor.

# WS\_D3 Series

## Model 3888D3

SUBMERSIBLE SEWAGE PUMPS

### APPLICATIONS

Used in a variety of residential, commercial and industrial applications such as:

- Sewage systems, Flood and Pollution Control, De-watering/Effluent, Farms, Hospitals, Trailer Courts, Motels

### SPECIFICATIONS

#### Pump:

- Maximum solid size: 2.5"
- Discharge size: 3", 125 # ANSI flange
- Maximum capacity: 470 GPM
- Maximum total head: 65 feet
- 300 Series stainless steel fasteners
- 20' Power cord
- Standard silicon carbide/silicon carbide outer seal

#### Motor:

- Maximum ambient temperature: 104° F (40° C) continuous duty, 140° F (60° C) intermittent duty
- Rated for continuous duty when fully submerged
- Insulation: Class F
- 60 Hertz
- Single row ball bearings
- 300 Series stainless steel keyed shaft

#### Single Phase:

- 1.5 - 5 HP; 208 and 230 volts
- Built-in thermal overloads with automatic reset
- Built-in capacitors

#### Three Phase:

- 1.5 - 5 HP; 200, 230, 460 and 575 volts
- Class 10 overload protection must be provided in control panel

### MOTORS

- Fully submerged in oil-filled chamber: High grade turbine oil surrounds motor for more efficient heat dissipation, permanent lubrication of bearings and mechanical seal for complete protection against outside environment.
- Class F insulation
- Designed for Continuous Operation: Pump ratings are within the motor manufacturer's recommended working limits and can be operated continuously without damage when fully submerged.
- Bearings: Upper and lower heavy duty ball bearing construction for precision positioning of parts and to carry thrust loads.
- Power Cable: Severe duty rated, oil and water resistant. Epoxy seal on motor end provides secondary moisture barrier in case of outer jacket damage and to prevent oil wicking. 20 foot standard with optional lengths available.
- O-ring: Assures positive sealing against contaminants and oil leakage.

### AGENCY LISTINGS




Tested to UL 778 and CSA 22.2 108 Standards  
By Canadian Standards Association  
File #LR38549

### MODEL AND MOTOR INFORMATION

Order Number	HP	Phase	Volts	RPM	Impeller Diameter (in.)	Maximum Amps	Locked Rotor Amps	KVA Code	Power Cable	Full Load Motor Efficiency %	Resistance		Weight (lbs.)		
											Start	Line-Line			
WS1518D3M	1.5	1	208	1750	5.25	15.0	50.8	B	14/3	80	1.1	0.9	192		
WS1512D3M			230			12.5	29.5	E		70	1.4	1.8			
WS1538D3M		3	200			11.5	40.9	H	14/4	81	NA	1.7		190	
WS1532D3M			230			10.0	40.0	F		83		2.3			
WS1534D3M			460			5.0	20.0	F		83		9.3			
WS1537D3M			575			4.0	14.4	H		74		14.8			
WS1518D3		1	1		208	6.50	15.0	50.8	B	14/3	80	1.1	0.9	192	
WS1512D3					230		12.5	29.5	E		70	1.4	1.8		
WS1538D3			3		200		11.5	40.9	H	14/4	81	NA	1.7		190
WS1532D3					230		10.0	40.0	F		83		2.3		
WS1534D3					460		5.0	20.0	F		83		9.3		
WS1537D3					575		4.0	14.4	H		74		14.8		
WS2018D3	2	1	208	7.00	19.0	50.8	B	14/3	80	1.1	0.9	196			
WS2012D3			230		16.0	36.9	D		75	1.4	1.5				
WS2038D3		3	200		11.5	40.9	H	14/4	81	NA	1.7		194		
WS2032D3			230		10.0	40.0	F		83		2.3				
WS2034D3			460		5.0	20.0	F		83		9.3				
WS2037D3			575		4.0	14.4	H		74		14.8				
WS3018D3	3	1	208	7.25	25.5	50.8	B	10/3	80	1.1	0.9	205			
WS3012D3			230		21.5	46.4	C		79	1.0	1.0				
WS3038D3		3	200		15.2	53.8	G	14/4	85	NA	1.3		200		
WS3032D3			230		12.0	49.5	H		83		1.9				
WS3034D3			460		6.0	24.8	H		83		7.5				
WS3037D3			575		4.8	17.3	G		78		11.6				
WS5012D3	5	1	230	8.00	26.5	57.7	A	10/3	80	1.0	0.8	210			
WS5038D3			200		18.8	73.9	F		84	0.9					
WS5032D3		3	230		16.4	63.6	E	10/4	85	NA	1.2		205		
WS5034D3			460		8.2	31.8	E		85		4.8				
WS5037D3			575		6.8	22.8	E		80		7.4				

### MATERIALS OF CONSTRUCTION




Item No.	Part Name	Material				
		Standard	Optional			
1	Impeller, non-clog	1003	1179			
2	Castings	1003				
3	Shaft-keyed	300 Series SS				
4	Fasteners	300 Series SS				
5	Ball bearings	Steel				
6	Power cable	STOW, 20 feet	Additional lengths			
7	O-ring	BUNA-N				
8	<b>Outer Mech. Seal</b>	<b>Service</b>	<b>Rotary</b>	<b>Stationary</b>	<b>Elastomers</b>	<b>Metal Parts</b>
	OPT	Heavy duty	Silicon Carbide	Tungsten Carbide	BUNA-N	300 Series SS
	STD	Mild abrasives	Silicon carbide		BUNA-N	300 Series SS
<b>Material Code</b>		<b>Engineering Standard</b>				
1003		Cast iron – ASTM A48 Class 30				
1179		Silicon bronze – ASTM C87600				

### PERFORMANCE RATINGS (gallons per minute)

Series No. ▶	WS15D3M	WS15D3	WS20D3	WS30D3	WS50D3
<b>HP ▶</b>	1½	1½	2	3	5
<b>RPM ▶</b>	1750				
<b>Total Head Feet of Water</b>	10	160	300		
	15	90	260	320	
	20		210	280	350
	25		160	235	310
	30		100	185	265
	35			130	210
	40			60	160
	45				100
	50				
	55				
	60				

METERS FEET




## APPLICATION DATA AND CONSTRUCTION DETAILS

Maximum Solid Size	2.5"	
Minimum Casing Thickness	5/16"	
Casing Corrosion Allowance	1/8"	
Maximum Working Pressure	30 PSI	
Maximum Submergence	50 feet	
Minimum Submergence	Fully submerged for continuous operation	
	6" below top of motor for intermittent operation	
Maximum Environmental Temperature	40° C (104° F) continuous operation, 60° C (140° F) intermittent operation	
Power Cable - Type (See Motor Information for AWG data/size.)	Type SJTOW: single phase, 1½ and 2 HP	
	Type STOW: single phase, 1½ - 3 HP and 5 HP, 460 V	
	Type STOW: single phase, 3 and 5 HP, three phase 5 HP, 230 V	
Motor Cover, Bearing Housing, Seal Housing, Casing	Gray Cast Iron - ASTM A48, Class 30	
Impeller - Standard, Optional	Gray Cast Iron - ASTM A48 or Cast Bronze - ASTM B584 C87600	
Motor Shaft	AISI 300 Series Stainless Steel	
Motor Design	NEMA 56 Frame, oil filled with Class F Insulation	
Motor Overload Protection	Single phase: on winding thermal overload protection auto reset	
	Three phase: requires Class 10 overloads in control panel	
External Hardware	300 Series Stainless Steel	
Impeller Type	Semi-open with pump out vanes on back shroud	
Oil Capacity - Seal Chamber	1.5 quarts	
Oil Capacity - Motor Chamber	1½-5 HP single and three phase: 7 quarts	
Mechanical Seals - Standard	Upper	Carbon/Ceramic; Type 21
	Lower	Silicon Carbide/Silicon Carbide; Type 31
Mechanical Seals - Optional Lower	Silicon Carbide/Tungsten Carbide; Type 31	

## DIMENSIONS

(All dimensions are in inches. Do not use for construction purposes.)



**xylem**  
Let's Solve Water

Xylem, Inc.  
2881 East Bayard Street Ext., Suite A  
Seneca Falls, NY 13148  
Phone: (866) 325-4210  
Fax: (888) 322-5877  
[www.xylem.com/brands/gouldswatertechnology](http://www.xylem.com/brands/gouldswatertechnology)

Goulds is a registered trademark of Goulds Pumps, Inc. and is used under license.  
SKF is a registered trademark of Aktiebolaget SKF, Sweden.  
© 2012 Xylem Inc. B3888D3 R1 April 2012