


# ENSORB® SUPER ABSORBENT™



### PRODUCT & DISPOSAL COSTS COMPARISON

(Based on 1 quart of motor oil)



### FEATURES:

- 15 to 20 times the absorption capacity of clay-based products.
- Virtually unlimited uses as a dry absorbent that is safe in all applications.
- Picks up all liquids, of any viscosity, off any hard surface, leaving that surface clean and dry.
- Turns the spilled liquid into a solid that can be disposed of easily.
- Lightweight and simple to use, it dramatically reduces clean up costs, as well as the ever-increasing costs of disposal.
- Not injurious to soil, cement, asphalt, tile, plants, animals, or humans.
- Contains no reactive chemicals, is not toxic or flammable.

\*Note: Cannot be used with Hydrofluoric Acid (HF).

ENSORB® Super Absorbent™ has unlimited uses! Immediately absorbing liquids of any viscosity ENSORB® leaves surfaces clean and dry.

- Extraordinary versatility in absorbing any kind of liquid or semi-liquid on contact and permanently encapsulates absorbed materials. This includes all animal, vegetable, mineral, petroleum, and chemical liquids\*.
- Non-Biodegradable and is environmentally safe and friendly.

### ENSORB® SUPER ABSORBENT™

| Part #     | Description             | Weight lb. (kg) | Quantity |
|------------|-------------------------|-----------------|----------|
| ENP D225   | 1.5 Cubic Ft. Bag       | 15 (6.8)        | 1/Case   |
| ENP D503   | 1 Gallon Jug Dispenser  | 3 (1.4)         | 1/Case   |
| ENP D503CS | 1 Gallon Jug Dispensers | 22 (9.8)        | 6/Case   |
| ENP D208CS | 1 Quart Zip Seal Bags   | 8 (3.6)         | 12/Case  |

## ENSORB® SUPER CLEANER/DEGREASER

ENSORB® Super Cleaner/Degreaser™ is a versatile multiple-use concentrate. Water-based and environmentally friendly, it's a powerful cleaner that leaves surfaces clean and free of residue.



### ENSORB® SUPER CLEANER/DEGREASER

| Part #     | Description     | Weight lb. (kg) | Quantity case |
|------------|-----------------|-----------------|---------------|
| ENP D312CS | 1 Gallon Bottle | 40 (18.1)       | 4/Case        |