



**JUSTRITE®**

**New!**

**Product**

**Eco-friendly**

**ESSENTIALS**

# EcoPolyBlend™ Spill Control Pallets

The first and only spill control line made of recycled polyethylene!

Eco-friendly pallets are made of up to 100% recycled polyethylene, making them twice as good for the environment! They not only protect against groundwater contamination, they also utilize post-industrial material that might have otherwise been discarded into the waste stream.

Quality engineered with a robust design, pallets withstand the toughest environments for superior spill control. Durable, UV-protected EcoPolyBlend™ polyethylene is nearly impervious to chemical attack from hazardous acids, caustics and solvents. Seamless construction eliminates leaks even if a 55-gallon (200L) drum fails and completely empties its contents.

Fully compliant, Justrite® EcoPolyBlend™ Pallets feature oversized leakproof sumps that meet or exceed regulations. Sturdy, removable grates are nearly 2-1/2" (64mm) thick for superior crack resistance. Self-locating, they reduce the chance of grate "ride-up" and remove for quick sump inspection and cleaning.

Two drum and 4-drum square pallets include wide forklift pockets for easy relocation. Square pallet may be equipped with an optional Ramp to facilitate loading and unloading of heavy drums.

### Meets or Exceeds

EPA 40 CFR 264.175

NFPA 1 the Uniform Fire Code 60.3.2.10

International Fire Code 2704.2.3

Spill Prevention, Control and Countermeasures (SPCC) Compliant

NFPA 30 9.13.1 and OSHA 29 CFR 1910.106(e)(2)(iii)



**Black = 100% recycled content**  
**Yellow = 35% recycled content**

"Eco black" pallets are made of 100% recycled material. Their dark color camouflages dirt and keeps workplaces looking clean.

Yellow pallets are available for high visibility or liquid segregation when desired; material content consists of virgin poly sumps with 100% recycled grates ... resulting in a total of 35% recycled content.

Yellow Ramp non-recycled.



JUSTRITE® EcoPolyBlend™ Spill Control Pallets							recycled content	
							100%	35%
Product Description	Sump Capacity Gallons (L)	Load Bearing Capacity Lbs./kgs	Nominal Outside Dimensions W x D x H (mm)	Compliance	Ship Wt. Lbs./Kgs.	Model No. Black	Model No. Yellow	
2 drum	66 (250)	2500/1134	49" x 25" x 18" (1245 x 635 x 457)	EPA, SPCC, U, O	44/20	28623	28622	
2 drum w/drain	66 (250)	2500/1134	49" x 25" x 18" (1245 x 635 x 457)	EPA, SPCC, U, O	44/20	28625	28624	
3 drum	75 (284)	3750/1701	73" x 25" x 11 5/8" (1854 x 635 x 295)	EPA, SPCC, U, O	58/26	28627	28626	
3 drum w/drain	75 (284)	3750/1701	73" x 25" x 11 5/8" (1854 x 635 x 295)	EPA, SPCC, U, O	58/26	28629	28628	
4 drum square	73 (276)	5000/2268	49" x 49" x 10 1/4" (1245 x 1245 x 260)	EPA, SPCC, U, O	70/32	28635	28634	
4 drum square w/drain	73 (276)	5000/2268	49" x 49" x 10 1/4" (1245 x 1245 x 260)	EPA, SPCC, U, O	70/32	28637	28636	
4 drum In-line	75 (284)	5000/2268	97" x 25" x 9" (2464 x 635 x 229)	EPA, SPCC, U, O	77/35	28631	28630	
4 drum In-line w/drain	75 (284)	5000/2268	97" x 25" x 9" (2464 x 635 x 229)	EPA, SPCC, U, O	77/35	28633	28632	

### Spill Pallet Accessory (non-recycled)

Model No. Ship Wt.

Yellow Ramp for 4 drum square	1000/454	49" x 33" x 10 1/2" (125 x 84 x 26)	28620	40/18
-------------------------------	----------	-------------------------------------	-------	-------

(over)

©2009 Justrite



Phone: 800-798-9250

Fax: 800-488-5877

www.justritemfg.com

**Breaking new ground! Up to 100% recycled!**

# EcoPolyBlend™ Accumulation Centers

**The only spill platforms made from recycled polyethylene!**

Get reliable, high performance spill control and help reduce landfills by using recycled products. These economical, low profile secondary containment platforms are eco-friendly— made of up to 100% recycled, post-industrial, durable polyethylene that might have otherwise been discarded into the waste stream.

Long lasting EcoPolyBlend™ polyethylene is nearly impervious to chemicals, including acids and corrosives. Accumulation Centers feature a seamless design to ensure any leaks or spills are captured in the sump, before they reach floor drains or create a slip hazard. Sturdy grates are nearly 2-1/2" (64mm) thick for superior crack resistance. Self-locating, they reduce the chance of grate "ride-up" and remove for easy cleaning.

Modular centers offer the ability to create a customized system. As capacity needs increase, use optional Joining Clips to firmly lock units together and expand storage space. Sumps remain separate and clips can be removed for easy repositioning. In applications calling for a continuous sump, optional Sump-to-Sump™ Drain Kit (includes joining clips and transfer tube), allows centers to be joined together on-site for full compliance to EPA and fire codes when combined sump capacities need to meet 66 gallons (250L).

Optional companion Ramp facilitates movement of heavy drums and features anti-skid ribs for maximum safety. It can be located anywhere on any 2-drum or larger Center.

For compliant storage using units 4-drum and smaller, use Sump-to-Sump Drain Kit to reach needed capacity.

**6 and 8 Drum Centers Meet or Exceed Regulations**  
**EPA 40 CFR 264.175**  
**NFPA 1 the Uniform Fire Code 60.3.2.10**  
**International Fire Code 2704.2.3**  
**Spill Prevention, Control and Countermeasures (SPCC) Compliant**  
**NFPA 30 9.13.1 and OSHA 29 CFR 1910.106(e)(2)(iii)**



**Black = 100% recycled content**  
**Yellow = 45% recycled content**

**"Eco black" platforms** are made of 100% recycled material. Their dark color camouflages dirt and keeps workplaces looking clean. **Yellow platforms** are available for high visibility or liquid segregation when desired; material content consists of virgin poly sumps with 100% recycled grates ... resulting in a total of 45% recycled content.

**Yellow ramp** non-recycled.



JUSTRITE® EcoPolyBlend™ Accumulation Centers							recycled content	
							100%	45%
Product Description	Sump Capacity Gallons (L)	Load Bearing Capacity Lbs./Kgs	Nominal Outside Dimensions W x D x H (mm)	Compliance	Ship Wt. Lbs./Kgs.	Model No. Black	Model No. Yellow	
1 drum	12 (45)	1250/567	25" x 25" x 5 1/2" (635 x 635 x 140)	—	17/8	28653	28652	
2 drum	24 (90)	2500/1134	49" x 25" x 5 1/2" (1245 x 635 x 140)	—	32/15	28655	28654	
4 drum	49 (185)	5000/2268	49" x 49" x 5 1/2" (1245 x 1245 x 140)	—	61/28	28657	28656	
6 drum	73 (276)	7500/3402	73" x 49" x 5 1/2" (1854 x 1245 x 140)	EPA, SPCC, U, O	91/41	28659	28658	
8 drum	98 (371)	10,000/4536	97" x 49" x 5 1/2" (2464 x 1245 x 140)	EPA, SPCC, U, O	122/55	28661	28660	

## Accumulation Center Accessories (non-recycled)

	Model No.	Ship Wt.
Yellow Ramp for 2 drum and larger	1000/455	48" x 33" x 6 1/4" (1219 x 838 x 159)
Joining Clips	28926	4" x 2" (102 x 51) one pair, stainless steel
Sump-to-Sump™ Drain Kit	28927	One pair stainless steel joining clips, one pair rubber grommets, one PTFE transfer tube

(over)