

# FISSURED™

## Square Lay-in & Tegular

medium texture

Recycled Content: **Up to 51%**

armstrong.com/greengenie

### LEED® Credits

Energy	Waste Mgmt	Recycled Content	Local Materials	Renewable Materials	Daylight & Views
	✓	✓	✓	✓	✓

Location Dependent

### LEED for Schools

Acoustics	Low Emitting or CHPS
	✓

\$\$\$\$\$

### Key Selection Attributes

- Economical
- Directional fissured image

### Typical Applications

- Utility rooms
- Discount stores

### Color



White (WH)



Fissured Angled Tegular with Prelude® 15/16" Exposed Tee grid (Pg. 215)

### Visual Selection

### Performance Selection Dots represent highest level of performance.

Edge Profile	Suspension Detail Dwg. Pgs. 226-228	Item No.	Dimensions	UL Classified		Fire Rating	Light Reflect	Sag Resist	Anti-Microbial	Durable	Recycle Program
				Acoustics NRC	CAC						
<b>FISSURED Square Lay-in</b>											
	1	<b>756</b> <b>756M</b>	2' x 2' x 5/8" 600 x 600 x 15mm	<input type="checkbox"/>	0.55 30	Class A	0.81	Standard	–	Standard	Yes •
	1	<b>896</b> <b>896M</b>	2' x 2' x 5/8" 600 x 600 x 15mm	<input type="checkbox"/>	0.55 35	Fire Guard	0.81	Standard	–	Standard	•
	1	<b>755</b>	2' x 4' x 5/8"	<input type="checkbox"/>	0.55 30	Class A	0.81	Standard	–	Standard	•
	1	<b>895</b> <b>895M</b>	2' x 4' x 5/8" 600 x 1200 x 15mm	<input type="checkbox"/>	0.55 35	Fire Guard	0.81	Standard	–	Standard	•
<b>FISSURED Tegular</b>											
	6	<b>705</b> <b>705M</b>	2' x 2' x 5/8" 600 x 600 x 15mm	<input type="checkbox"/>	0.55 30	Class A	0.81	Standard	–	Standard	•
	6	<b>815</b>	2' x 2' x 5/8"	<input type="checkbox"/>	0.55 35	Fire Guard	0.81	Standard	–	Standard	•

### Suspension Systems



### Physical Data

**Material**  
Wet-formed mineral fiber

**Surface Finish**  
Factory-applied latex paint

**Fire Performance**  
ASTM E84 and CAN/ULC S102 surface burning characteristics. Flame Spread Index 25 or less. Smoke Developed Index 50 or less. (UL labeled) Fire Guard™: A fire resistive ceiling when used in applicable UL assemblies

**ASTM E1264 Classification**  
Type III, Form 2, Pattern C D  
Fire Class A

**VOC/Formaldehyde Emissions**  
Meets CA Dept. of Health Services Standard Practice for the testing of VOC Emissions and is listed on CHPS High Performance Products Database for Low-Emitting Materials.

**Insulation Value**  
755, 756, 895, 896 –  
R Factor – 1.5 (BTU units)  
R Factor – 0.26 (Watts units)  
705, 815 –  
R Factor – 1.6 (BTU units)  
R Factor – 0.28 (Watts units)

**Warranty Information**  
See warranty details in the back of this catalog

**Weight; Square Feet/ Carton**  
705 – 0.69 lbs/SF; 64 SF/ctn  
755 – 0.66 lbs/SF; 96 SF/ctn  
756 – 0.67 lbs/SF; 64 SF/ctn  
815 – 1.08 lbs/SF; 48 SF/ctn  
895, 896 – 1.09 lbs/SF; 64 SF/ctn