

Universal Features

Available in 25 and 50 foot lengths these high quality wash down hoses are ideal for use in the food processing industry. Premium wrapped safety orange with a maximum pressure of 300 psi and a maximum temperature of 200 F. The hoses are assembled with brass or stainless steel fittings. 3/4" I.D. and 1 1/4" O.D.

Models H25 and H50

Features

- 3/4" GHT swivel fitting on nozzle end of hose
- 3/4" Female flare with a 3/4" Male flare x 3/4" NPT adapter on water source end



Model H25



Model H50


Universal Features

Hot and Cold water mixing stations are designed to mix hot and cold water in any desired amount. Equipped with a temperature gauge that accurately indicates the wash water's temperature. NOTE: Not suitable for steam service.

Model M1

Features

- Maximum temperature 200 F/90 C
- Maximum pressure 150 psi
- Standard globe valves
- High – Low adjustable flow rate



Model M1

Model M1 with H25 hose and N1B nozzle sold separately.