



- G1643** Emergency Shower, Horizontally Mounted, Plastic Shower Head
- G1643SSH** Emergency Shower, Horizontally Mounted, Stainless Steel Shower Head

**Application:** Emergency shower for horizontal mounting.

**Shower Head:** 10" diameter. Shower head is orange ABS plastic (G1643) or stainless steel (G1643SSH).

**Valve:** 1" IPS chrome plated brass stay-open ball valve. Valve is US-made with chrome plated brass ball and Teflon® seals. Furnished with stainless steel actuating arm and 29" stainless steel pull rod.

**Pipe and Fittings:** 1" IPS galvanized steel nipple with orange ABS plastic elbow (G1643) or galvanized street elbow (G1643SSH).

**Supply:** 1" NPT female inlet.

**Sign:** ANSI-compliant identification sign.


### Available Options

- PCC** All-polished chrome plated brass construction.
- GRN** Safety green ABS plastic shower head.
- YEL** Safety yellow ABS plastic shower head.
- PCH** Polished chrome plated cast brass shower head.
- FC20** Regulates shower flow rate to 20 GPM.
- SC** Self-closing ball valve. *Note: Emergency showers with self-closing valves do not comply with ANSI Z358.1-2009.*
- AP280-100 ELECTRIC LIGHT AND ALARM HORN**  
Flashing light and horn serve to summon assistance when shower is activated.
- TMV** G3800 thermostatic mixing valve precisely blends hot and cold water to deliver warm (tepid) water as required by ANSI Z358.1-2009. Refer to "Tempering Units" section for complete technical and product selection information.
- AP250-015 MODESTY CURTAIN**  
Modesty curtain for horizontal shower installation.





- **G1643** Emergency Shower, Horizontally Mounted, Plastic Shower Head
- **G1643SSH** Emergency Shower, Horizontally Mounted, Stainless Steel Shower Head



THIS SPACE FOR ARCHITECT/ENGINEER APPROVAL

Due to continuing product improvement, the information contained in this document is subject to change without notice. All dimensions are ± 1/4" (6mm). rev. 0114

Sign Included

