

# MAGIC WRENCH<sup>®</sup> AEROSOL

## SUPER PENETRANT

### DESCRIPTION

**MAGIC WRENCH<sup>®</sup>** Super Penetrant attacks rust and corrosion quickly and safely to free corroded parts, loosen nuts and aid in the disassembly of mechanical components. Versatile synthetic formula penetrates, lubricates, removes moisture and protects chains, cables, slides and other moving parts. Silicone free. Nonevaporative. Safe on all metals and plastics. Excellent for both food grade and non-food grade applications. Low V.O.C. (Volatile Organic Components) formula assures not only an environmentally responsible product, but more active ingredients to enhance product performance.

- NSF H-1 Registered #048230
- Penetrates Fast
- Synthetic Fluids
- Biodegradable
- Destroys Rust
- Lubricates
- Safe on Metal & Plastic
- Convenient aerosol package
- Low VOC Formula
- Silicone Free
- Ozone Safe
- Nonevaporative

### APPLICATIONS

**MAGIC WRENCH** is a premium, synthetic product that may be used as a light machine oil, penetrating oil or rust preventive. Excellent for use on equipment such as chains, linkages, cams and slides, stirrups on bottle-filling machines, valves, pins, hinges, cables, etc. In addition, **MAGIC WRENCH** is an ideal product for the lubrication and conditioning of air tools.

NSF H-1 Registered (Reg. No. 048230). Conforms to FDA Regulation CFR 21, Section 178.3570 for incidental Food Contact.

### PRODUCT CHARACTERISTICS

|                                     |  |
|-------------------------------------|--|
| Appearance                          | Clear, pale yellow fluid w/ faint odor |
| Fluid Type                          | Ester, PAO & White Oils                |
| Propellant                          | Hydrocarbon                            |
| ISO Viscosity Grade                 | 32                                     |
| SAE Viscosity Grade                 | 10                                     |
| Density (lb/gal)                    | 6.92                                   |
| Specific Gravity                    | 0.83                                   |
| Flash Point (ASTM D-92)             | >450°F (232°C)                         |
| Copper Strip Corrosion (ASTM D-130) | 1B                                     |
| Pour Point (ASTM D-97)              | 10°F (-12°C)                           |
| Spray Pattern (from 12" distance)   | 1" cone                                |
| Service Rating                      | -60°F (-51°C) to 350°F (177°C)         |
| NFPA 30B Storage Class              | Level II                               |
| VOC Content (Without Propellant)    | 10g/Liter                              |
| Flame Extension Test                | 6" - 8"                                |

### PACKAGING

| Code No. | Container Size | Container |
|----------|----------------|-----------|
| 39541    | 13 oz.         | Aerosol   |

### LIMITED WARRANTY

Jet-Lube, Inc. makes the Limited Express Warranty that at the date of delivery, this product shall be free from defects in Jet-Lube, Inc. materials and workmanship.

This Limited Express Warranty is expressly in lieu of any other express or implied warranties, including any implied warranty of merchantability or fitness for a particular purpose, and of any other obligation on the part of Jet-Lube, Inc.

The sole remedy for breach of the Limited Express Warranty shall be the refund of the purchase price. All other liability is negated and disclaimed, and Jet-Lube, Inc. shall not be liable for incidental or consequential damages.

### CORPORATE LOCATIONS

Houston, Texas—World Headquarters

0813

Maidenhead, England

Edmonton, Canada

JET-LUBE, INC.  
4849 HOMESTEAD RD.,  
P.O. BOX 21258 (77226-1258)  
HOUSTON, TX 77028

FOODGRADE  
FOODGRADE  
FOODGRADE  
FOODGRADE  
FOODGRADE