

LOCTITE® Fixmaster® Floor Fill™

December 2012

PRODUCT DESCRIPTION

LOCTITE® Fixmaster® Floor Fill™ provides the following product characteristics:

Technology	Epoxy
Chemical Type	Epoxy
Appearance (uncured)	Grey Liquid
Components	Three components - requires mixing
Mix Ratio, by volume - Resin : Hardener to Filler	4.6 : 1 to 9.8
Mix Ratio, by weight - Resin : Hardener to Filler	16 : 3.2 to 80.8
Cure	Room temperature cure
Application	Flooring & grout
Specific Benefit	<ul style="list-style-type: none"> • 100 % solids • Non-shrinking • Chemical resistant • Outperforms concrete • Self-leveling • Easy to mix and use and has application versatility

LOCTITE® Fixmaster® Floor Fill™ is a non-shrinking 100% solids epoxy based system for repairing holes in floors, spalled areas, ramps, stairs, cracks in floors and for use in grouting applications. Once cured, it is stronger than concrete and bonds to almost any clean substrate and provides chemical resistance under typical dry service temperatures of -30 to 110 °C (-20 to 225F).

TYPICAL PROPERTIES OF UNCURED MATERIAL

Weight per volume	kg/L (lbs/gal)	1.09 to 1.18 (9.1 to 9.8)
Density @ 23 °C, g/cm³		2.38
Hardener:		
Density @ 23 °C, g/cm³		2.396
Mixed:		
Density @ 23 °C, g/cm³		2.38
Coverage		8.7 liters per 18 kg kit (532 in³ per 40 lb kit)
Flash Point - See MSDS		


TYPICAL CURING PERFORMANCE

Curing Properties

Gel Time @ 21 °C, minutes 40 to 50

Cure Speed vs. Temperature

The graph below shows the shear strength developed with time on grit blasted steel lap shears at different temperatures and tested according to ISO 4587.



TYPICAL PROPERTIES OF CURED MATERIAL

Physical Properties:

Volume Shrinkage, ISO 1675 %	0.66
Coefficient of Thermal Conductivity ASTM F 433, W/(m·K)	0.21
Glass Transition Temperature ISO 11359-2, °C	<-50
Coefficient of Thermal Expansion, ISO 11359-2, K ⁻¹ :	
Above Tg	166×10 ⁻⁶
Compressive Strength, ISO 604	N/mm² 90 (psi) (13,100)
Compressive Modulus, ISO 604	N/mm² 11,300 (psi) (1,633,000)
Flexural strength, ASTM D790	N/mm² 23 (psi) (3,370)
Flexural modulus, ASTM D790	N/mm² 6,430 (psi) (932,240)

Electrical Properties:

Volume Resistivity, IEC 60093, ohm-cm	780×10 ¹²
Surface Resistivity, IEC 60093, ohms	4.4×10 ¹⁵




TYPICAL ENVIRONMENTAL RESISTANCE


Lap Shear Strength, ISO 4587:
Grit Blasted Mild Steel (GBMS)

Hot Strength

Tested at temperature

**Heat Aging**

Aged at temperature indicated and tested @ 22 °C

**GENERAL INFORMATION**

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials.

For safe handling information on this product, consult the Material Safety Data Sheet (MSDS).

Directions for use:**Surface Preparation:**

1. Clean all dust, grease, latent concrete, or other foreign matter from the surface to be coated.

Mixing:

1. Remove all materials from the outer pail.
2. Pour resin contents into empty pail.
3. Add hardener contents to resin. Mix with electric drill and mixing paddle.
4. Add silica filler to the resin and hardener mixture and continue mixing until thoroughly mixed. Be sure to mix along sides and across bottom of pail.
5. At 25°C, the working time is 40 to 60 minutes and

functional cure time is 24 hours.

NOTE: To obtain a pourable consistency do not use all of the filler. However, when leaving out part of the filler the working time and cure time will be shorter

Technical Tips for Working With Epoxies

Working time and cure depends on temperature and mass:

- The higher the temperature, the faster the cure.
- The larger the mass of material, the faster the cure.

To speed the cure of epoxies at low temperatures:

- Store epoxy at room temperature.
- Pre-heat repair surface until warm to the touch.

To slow the cure of epoxies at high temperatures:

- Mix epoxy in small masses to prevent rapid curing.
- Cool resin/hardener component(s).

Not for product specifications

The technical data contained herein are intended as reference only. Please contact your local quality department for assistance and recommendations on specifications for this product.

Storage

Store product in the unopened container in a dry location. Material removed from containers may be contaminated during use. Do not return liquid to original container. Storage information may be indicated on the product container labeling. **Optimal Storage: 8 °C to 21 °C. Storage below 8 °C or greater than 28 °C can adversely affect product properties.** Henkel cannot assume responsibility for product which has been contaminated or stored under conditions other than those recommended. If additional information is required, please contact your local Technical Service Center or Customer Service Representative.

Conversions

$(^{\circ}\text{C} \times 1.8) + 32 = ^{\circ}\text{F}$
 $\text{kV/mm} \times 25.4 = \text{V/mil}$
 $\text{mm} / 25.4 = \text{inches}$
 $\mu\text{m} / 25.4 = \text{mil}$
 $\text{N} \times 0.225 = \text{lb}$
 $\text{N/mm} \times 5.71 = \text{lb/in}$
 $\text{N/mm}^2 \times 145 = \text{psi}$
 $\text{MPa} \times 145 = \text{psi}$
 $\text{N}\cdot\text{m} \times 8.851 = \text{lb}\cdot\text{in}$
 $\text{N}\cdot\text{m} \times 0.738 = \text{lb}\cdot\text{ft}$
 $\text{N}\cdot\text{mm} \times 0.142 = \text{oz}\cdot\text{in}$
 $\text{mPa}\cdot\text{s} = \text{cP}$

Note

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Henkel Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Henkel Corporation's products. Henkel Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Henkel Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

Trademark usage

Except as otherwise noted, all trademarks in this document are trademarks of Henkel Corporation in the U.S. and elsewhere. ® denotes a trademark registered in the U.S. Patent and Trademark Office.

Reference 0.0