

CC LUBE™

CLEAR, CLEAN, SEMI-SYNTHETIC MULTIPURPOSE LUBRICANT

DESCRIPTION

CC LUBE™ is a state-of-the-art, semi-synthetic, multi-purpose lubricant that combines an aluminum complex thickener for extreme water resistance with the latest synthetic ingredients and PTFE to create a totally transparent, long-lasting, high lubricity lubricant with unequalled quality and performance.

CC LUBE is clear, clean, colorless, nonstaining, nondrying, biodegradable and unsurpassed in reducing friction, extending machine and equipment life and preventing the formation of rust and corrosion over a broad temperature range of 0°F (-18°C) to 400°F (204°C). CC LUBE is NSF (H-1) Registered for use in Federally Inspected Meat and Poultry Plants.

- Nontoxic, Nonstaining
- Clear, Clean Lubricant
- Nondrying Formula
- Colorless/Odorless
- Contains PTFE
- NSF (H-1) Registered
- Prevents Rust, Corrosion
- Biodegradable
- Extremely Water Resistant
- Reduces Friction
- Available in Other Grades

APPLICATIONS

May be safely used on a variety of food processing equipment. CC LUBE is designed to eliminate hot water wash-out and has anti-bacterial additives to eliminate bacterial culturing. It may be used safely on a variety of surfaces including metal, plastic, rubber (viton, neoprene, buna & HSN), vinyl, stainless steel and nylon. CC LUBE is an ideal lubricant for roller, pillow block, needle and plain bearings that are used in cooking, processing and packaging of food products. It is a clear lubricant and will not stain cotton, polyester or Mylar fabrics.

Bearings

Gears

Valves

Conveyors Bushings

Bottling equipment

Belting for baking ovens

Food processing machinery

NSF (H-1) Reg. #048221
Conforms to FDA Regulations CFR 21 Section
178.3570 for Incidental Food Contact.

PRODUCT CHARACTERISTICS

Thickener	Aluminum Complex
Fluid Type	White Oils & Synthetics
Color/Appearance	Clear
Dropping Point (ASTM D-566)	500°F (260°C)
Specific Gravity	0.88
Density (lb/gal)	7.3
Additive Type	Organic, R&O, PTFE
Flash Point (ASTM D-92)	>430°F (221°C)
Autoignition Point (CALCULATED)	>500°F (260°C)
NLGI Grade	1-1½
Approx. Safe DN Limit	300,000
Penetration @77°F (ASTM D-217)	285-315
Copper Strip Corrosion (ASTM D-4048)	1A
4-Ball (ASTM D-2596)	
Weld Point, kgf	126
Load Wear Index	25
Wear Scar Diameter (ASTM D-2266)	0.7
Oxidation Resistance (ASTM D-942)	
PSI Drop, 100 hours	<5.0
Base Oil Viscosity (ASTM D-445)	
cSt @ 40°C	100 - 150
cSt @ 100°C	14.3 typ.

PACKAGING

Code No.	Container Size	Container
70550	14 oz.	Cartridge
70516	35 lb.	5 gal. drum
70524	120 lb.	15 gal. drum
70529	400 lb.	50 gal. drum

LIMITED WARRANTY

Jet-Lube, Inc. makes the Limited Express Warranty that at the date of delivery, this product shall be free from defects in Jet-Lube, Inc. materials and workmanship.

This Limited Express Warranty is expressly in lieu of any other express or implied warranties, including any implied warranty of merchantability or fitness for a particular purpose, and of any other obligation on the part of Jet-Lube, Inc.

The sole remedy for breach of the Limited Express Warranty shall be the refund of the purchase price. All other liability is negated and disclaimed, and Jet-Lube, Inc. shall not be liable for incidental or consequential damages.

0311

CORPORATE LOCATIONS

Houston, Texas—World Headquarters

Maidenhead, England

Edmonton, Canada



JET-LUBE, INC.
4849 HOMESTEAD RD.,
SUITE 232
HOUSTON, TX 77028