



0120-

Ⓒ  
LENGTH  
+3/32  
-1/16

.312 DIA HOLES  
CT'SK TO .390 DIA.

Ⓑ

PART NUMBER	LENGTH	IST FEED	PROGRESSION FEED
0120-7	7"	RBR	RBR
0120-16	16-1/2	1 @ 3"	1 @ 13.500
0120-25	25-1/2	1 @ 3"	2 @ 11.250
0120-28	28"	1 @ 3"	2 @ 12.500
0120-39	39-1/4	1 @ 3"	2 @ 12.500 1 @ 11.250
0120-48	48"	1 @ 3"	3 @ 15.000
0120-63	63"	1 @ 3"	4 @ 15.000
Ⓒ 0120-70	70-1/2	1 @ 3"	6 @ 11.250
0120-72	71-3/4	1 @ 3"	5 @ 13.750
0120-78	78"	1 @ 3"	5 @ 15.000

TOLERANCES UNLESS SPECIFIED: DECIMALS+OR-.005 FRACTIONS=OR-1/64 ANGLES=OR-1/2

JOHN STERLING CORPORATION RICHMOND, IL. 60071 U.S.A.		SURFACE	SCALE 1:1	POSITION - QUANTITY -
			#727 068-075 X 2.000 X CRCQ	
	DATE	NAME		
	9/12/96	R.KLUGE		
H	.312 DIA WAS .322 8/04 RK	CHECKED	TRAK MOUNT UPRIGHT	
G	ADD +3/32/-1/16 5-02	4284	STANDARD	
F	1/2 WAS 1/4 5-00 RK/G			
C	ADD -72 3-99	5721		
B	ADD PROG LEN 2-99	RK/G	SIZE	REV PAGE
A	ISSUED 11-98	5634	C-0120-	H -
STATE	CHANGES	DATE	NAME	FILENAME UNNAMED