

Hand Trucks Dual Grip

Model No.	Size W-H-D	Wheel Type	Ship Wt.
99676F	18" x 53-1/2" x 19-1/2"	Flat Free	33#
99676P	18" x 53-1/2" x 19-1/2"	Pneumatic	31#
99524F	18" x 60" x 19-1/2"	Flat Free	34#
99524P	18" x 60" x 19-1/2"	Pneumatic	32#
99676NC	18" x 53-1/2" x 16-1/4"	No Casters	29#
99524NC	18" x 60" x 16-1/4"	No Casters	23#

Stair glide wear strips are standard.

Wheels:

- 99676F & 99524F - (2) 3-1/2" x 10" Flat Free Wheels (#C559)
- 99676P & 99524P - (2) 3-1/2" x 10" Pneumatic Wheels (#C560)
- 99676NC & 99524NC - Includes 5/8" DIA. Axle

Replacement:

47092.... Stair Glide Wear Strips (2).



- Dual-grip handles.
- Lightweight, all welded aluminum construction.
- Weight Capacity = 750#.
- Removable/Replaceable nose plate.
- Hoop top, 1" pipe handle for easy handling.
- Lifetime warranty against rust and corrosion.



#99676

#99524



Hand Truck Pallet

Model No.	Size W-H-D	Wt. Cap.	Ship Wt.
99627	21" x 1-1/2" x 15-1/2"	750#	3#

Nose Plate Opening = 18-1/2"W x 3/4"H
Custom sizes available.

- Labor saving pallet allows movement of product without loading and unloading.
- Eliminates hand truck nose plate from scratching floors.
- All welded, lightweight aluminum construction.
- Designed to reduce damaged product.
- Ideal for route delivery trucks.
- Lifetime warranty against rust and corrosion.

You Tube > <http://www.youtube.com/user/NewAgeInd#p/u/8/9ifh6PsCQdc>



#99627

