

PIG® Leak Diverter Combination Kit for Roofs & Pipes

#TLS671 - 18" x 18"



Convenient bag kits are packed for fast response to overhead leaks, and offer extras to help make the job even easier.

- Hangs in problem spots to catch nuisance leaks and channel them to a floor drain or collection container
- Ideal for quick response to avoid downtime after a roof leak or for long-term prevention in leak-prone areas
- Impermeable tarp is vinyl coated for strength and durability; resists punctures, UV and mildew
- Hang with attached adjustable straps, then divert liquid away from leak with 25' drainage hose
- Quick connect set lets you attach drainage hose to leak diverter in seconds
- Flow rate of 3.33 gallons per minute when used with a 1/2" ID hose
- PIG Mat absorbent pads with "Caution, Watch Your Step" message soak up liquids from a wet floor
- PIG All-Purpose Wipers are ideal for cleaning up residue or wiping down kit components after use
- Carrying bag with adjustable shoulder strap has 18 pockets for additional tools or supplies
- PIG Pipe Leak Diverter hangs easily to channel leaks to a floor drain or collection container
- Need a custom size or solution? Just call 1-800-HOT-HOGS (468-4647)



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com

One Pork Avenue • Tipton PA 16684-0304

© 2014 New Pig Corporation. All rights reserved.
PIG and the PIG logo are trademarks in the U.S. and other countries.

ITEM: TLS671 - Pg 1 of 2

TLS671 Specifications

Use With:	Pipes & Roofs
Color:	Translucent
Dimensions:	ext. dia. 18" x 18" H
Drainage Hose Included:	Yes
Flow Rate:	3.33 gal. per Minute
Grommets/D-Rings:	N/A
Hanging Straps Included:	Yes
Hose Connector:	.75" w/ Quick Connect
Installation Method:	Hanging Straps
Thickness:	16 mil
Sold as:	1 each
Weight:	16.5 lbs.
# per Pallet:	36
Composition:	Leak Diverter - 67% PVC, 33% Polyester Hose - PVC Straps - Rubber

Includes:	Mats - Polypropylene Carrying Bag - Nylon 1 - 18" Ext. Dia. x 18" H Leak Diverter 1 - 5' L x 5' W Leak Diverter 1 - 25' L Drainage Hose 1 - 10' L Drainage Hose 4 - 19" L Adjustable Hanging Straps 1 - 30 Pack Yellow Printed Message "CAUTION" PIG® Mat 2 - 25 Pack 1/4 Fold PIG® All-Purpose Wipers in a Poly Bag 1 - Pack PIG® Pipe Wrap for Pipe 2.5" to 4" Dia. 1 - Tube PIG® Multi-Purpose Repair Putty 1 - 24" L x 10" W x 12" H Nylon Carrying Bag
UNSPSC:	24141506

TLS671 Metric Equivalent

Dimensions:	ext. dia. 45.7cm x 45.7cm H
Weight:	7.5 kg

Technical Information

Warnings & Restrictions:

Chemical Resistance
Limited chemical-resistance; not suitable for temperatures over 190° F/88° C.
This product is subject to export restrictions and cannot be shipped to: Canada, European Union, Japan.

Technical Documents:

(Available at newpig.com)
Product Data Sheet (PDS)
Safety Data Sheet (SDS)
Chemical Compatibility (CCG)



New Pig

By Phone:
1-855-493-HOGS

Online:
newpig.com

Email:
hothogs@newpig.com