

S351 Humidity Stage Module

Description

The S351 Stage Module is used in conjunction with the W351 Humidity Control to add multiple staging capability. Using a Y350R, up to five S351s can be added to the W351 via the 5-pin, plug-together connector. Using a 24 VAC or greater external transformer, up to nine S351s can be added. The S351 has an SPDT output relay and three adjustments including offset (de-energize stage action from setpoint), humidification or dehumidification mode, and differential.

Features


- humidification or dehumidification mode, field selectable
- · adjustable differential and offset
- 5-pin connectors eliminate wiring between modules

Applications

Use for multiple staging for humidification/ dehumidification of clean rooms, computer rooms, or space humidity control.



S351




Technical Specifications

S351 Humidity Stage Module with Percent RH Scale							
Case and Cover Material		NEMA 1, high-impact thermoplastic					
Supply Voltage		24 volt power supply provided by Y350R or external 24 VAC transformer					
Power Consumption			1 VA max.				
Ambient Temperature	Operating		-30 to 150°F (-34 to 66°C)				
	Shipping		-40 to 185°F (-40 to 85°C)				
Ambient Humidity	Operating		10 to 90% RH non-condensing				
	Shipping		0 to 95% RH non-condensing				
Relay			SPDT enclosed relays, contacts rated at 10 amp non-inductive, 1/2 hp, 120/240 VAC				
Mounting			Surface or DIN rail				
Relay Contact Ratings							
Voltage, AC		120	208/240				
Full Load Amp		9.8	4.9				
Locked Rotor Amp			58.8	29.4			
Non-Inductive Amp 10 at 24/240 VAC							
Pilot Duty – 125 VA at 24/240 VAC							

Selection Chart

Code Number	Output	Differential	Offset
S351AA-1C	SPDT Relay	2 to 10% RH	2 to 30% RH



S351 Dimensions, in. (mm)

The performance specifications are nominal and conform to acceptable industry standards. For applications at conditions beyond these specifications, consult the local Johnson Controls office. Johnson Controls, Inc. shall not be liable for damages resulting from misapplication or misuse of its products. © 2009 Johnson Controls, Inc. www.johnsoncontrols.com