



Superior  
Manufacturing  
Group, Inc.

# 470 Marble Sof-Tyle™ Anti-Fatigue/Anti-Slip Matting

Available Colors: Blue, Walnut, Black, Gray, Beige



Good Better Best Superior



**Marble Sof-Tyle™** complements any décor with a smooth marble-pattern design providing comfort and ergonomic support for dry applications such as lab testing areas, check-out counters, order fulfillment lines, and pharmacies. The durable rubber top surface is combined with a dense closed cell foam base utilizing NoTrax® exclusive UniFusion™ technology virtually eliminating the possibility of de-lamination.



Test	Test Description	*Results
Compression Deflection	Test specimen is subjected to varying compression load levels and the resulting deflection was measured. The greater the deflection, the better the anti-fatigue properties. (Inches)	.473" (40 lbs/sq. inch)
Coefficient of Friction ASTM C1028-96	A neolite heel assembly with a predetermined load is pulled horizontally with a dynamometer to measure the force required to cause the assembly to slip.	.73
Abrasion Resistance ASTM D3884-01	Test specimen is subjected to the rubbing action of two abrading wheels under controlled conditions. Results measured in Weight loss (Grams)	18.90 Grams
Elongation ASTM D412	Test specimen is stretched at a specified rate until breaking point. The results are measured in weight needed to break, and % of size increase at breaking point.	(data currently unavailable)
Tear Strength ASTM D1004	This test is designed to measure the force required to initiate tearing. The maximum stress, usually found near the outset of tearing, is recorded as the tear resistance in pounds (force)	(data currently unavailable)
Hardness ASTM D2240	The hardness of a test sample is measured by means of a type A Shore Durometer. The Durometer measures the penetration of its specified indenter forced into the test material under specified conditions	(data currently unavailable)
Critical Radiant Flux ASTM E648-94A	The test result is an average critical radiant flux (watts/square cm) which indicates the level of radiant heat energy required to sustain flame propagation in the flooring system.	(data currently unavailable)

\*All testing of NoTrax® floor matting has been performed by an independent testing laboratory.



- Utilizes NoTrax® exclusive UniFusion™ bond
- Durable SBR Rubber top surface
- Dense closed cell PVC foam base
- Top surface easy to sweep clean
- Overall thickness: 1/2"
- All four sides are beveled to minimize trip hazards
- Stock Sizes: 2' x 3', 3' x 5', 3' x 12'
- Roll Sizes: 2' x 75', 3' x 75', 4' x 75'
- Custom sizes available in 2', 3', and 4' widths



Anti-Fatigue



Custom Lengths



RESULTS from INDEPENDENT TEST LABS & PRESENTED as COMPARISONS to OTHER NoTRAX® FOOD SERVICE MATS