


Standard features

- Waterproof
- Impact resistant
- Conditional lifetime guarantee
- Crushproof
- Dustproof
- Powerclaw™ latching system
- Soft grip foldable handle
- Lightweight NK-7™ resin
- Padlockable
- 100% stainless steel hardware
- High performance gasket
- Automatic pressure release valve
- Molded-in bezel system
- Integrated lid stay
- Stackable
- Meets airline carry-on regulations

Case specifications

Exterior dimensions	L9.1" x W6.8" x H3.8" L231mm x W173mm x H97mm
Interior dimensions	L7.4" x W4.9" x H3.1" L188mm x W124mm x H79mm
Weight (empty)	1.3 lbs 0.6 kg
Lid depth	0.5" 13mm
Base depth	2.6" 66mm
Material	lightweight NK-7™ resin
Max buoyancy	4 lbs 2.0 kg
Temperature range	Min -20°F (-29°C) Max 140°F (60°C)
Airline carry-on	yes
Watertight (IP67)	yes
Warranty	conditional lifetime guarantee

Available options



Certifications

testing in progress

ATA 300	Impact test
ASTM D4169	Falling rain - Vibration - Drop tests
Mil-STD-810F	Immersion test
IP 67	Ingress protection tests (dust & immersion)

Packaging specifications

Quantity per pack	1
Pack dimensions	L9.3" x W4.1" x H7.2" L236mm x W104mm x H183mm
Pack weight (no foam)	1.5 lbs 0.7 kg

Available colors



Masterpack specifications

Items per masterpack	10
Masterpack dimensions	L21.3" x W9.9" x H15.7" L541mm x W251mm x H399mm
Masterpack weight	16.1 lbs 7.3 kg