

Available Colors: Black, Orange, Yellow, Terra Cotta



### Specialty




For custom configurations performed on-site, the M.D. Ramp System® is made of 100% nitrile rubber, and fit the male/female locking system of the Cushion-Ease® family of floor mats. All ramp lengths are beveled and molded with mitered corners and a protruding tab that locks together the two adjoining ramps for a secure, professional corner.

Test	Test Description	*Results
ASTM D-412	Tensile / Elongation	Tensile: min 900 psi Elongation: min 300%
ASTM D-2240	Durometer (Shore A)	50
ASTM D-1171	Ozone (Method A)	No Noticeable Effect
ASTM D-2589/CPSC FF-170	Surface Flammability/Carpets and Rugs	Pass

\*All testing of NoTrax® floor matting has been performed by an independent testing laboratory.

11/2014

Product	Top Surface	Ramps
650FR - Fire Retardant	Perforated	651
656FR - Fire Retardant	Solid	651
850FR - Fire Retardant/GSII	Perforated	551, 651, or 851
856FR - Fire Retardant/GSII	Solid	551, 651, or 851
660 - (ESD) Dissipative	Perforated	654
661 - (ESD) Dissipative	Solid	654
662 - Anti-Bacterial	Perforated	652
663 - Brake Fluid Resistant	Perforated	653
863 - Brake Fluid Resistant/GSII	Perforated	653
664 - Conductive	Perforated	654
665 - Conductive	Solid	654



Custom



Resistant

- 100% Nitrile Rubber
- Available in corresponding rubber compounds (See Solutions Chart)
- Thickness: 3/4"
- Ramp Width: 2"
- Stock Sizes: 2' Male, 3' Male, 3' Female, 5' Male, 5' Female
- For use with any Cushion-Ease® family products