

INDUSTRIAL 3-STRAND TWISTED 100% NYLON

High quality 100% nylon ropes for industrial use. All sizes above 5/16" diameter utilize plied yarns manufactured in a four stage process. Manufactured from specific grade raw material sourced from well known manufacturers. Nylon filament is steam heat set prior to twisting to reduce rope shrinkage in the field. Nylon has the highest stretch, strength, and shock absorbency of any synthetic rope.

COLOR: WHITE

PRODUCT NUMBER	STD	DIAMETER			LENGTH		AVG BREAK	LINEAR DENSITY		WEIGHT	
		IN	MM	CIRC	FT	M	STRENGTH	LBS/100'	KTEX	LBS	KG
430120-WHT-00600-05123	X	3/8"	10	1 1/8"	600'	182.9	3795	3.55	52.84	21.3	9.66