# <section-header><section-header>

# Slim design, unlimited possibilities

Offering design freedom in a slim, compact housing, Philips Advance e-Vision TrakStick and Mini Square electronic ballasts for 20W, 39W, 50W and 70W metal halide lamps are ideal for a variety of downlighting, track lighting and accent lighting applications. They provide an energy-efficient, cost-effective alternative to halogen and first generation ceramic metal halide lighting.

#### Features

- All metallic enclosures
- $\cdot$  90°C maximum case temperature rating
- $\cdot$  Superior lamp wattage regulation
- Enhanced safety features include automatic lamp power control, lamp monitoring and end-of-life (EOL) detection
- IntelliVolt multiple-voltage technology (operates 120 to 277V, 50/60 Hz)

#### Benefits

- Superior heat transfer relative to plastic, enhancing safety and durability
- $\cdot$  Optimizes lamp color quality over life
- Minimizes lamp-to-lamp variations
- Reduction of lamp overpowering and/or thermal stress by shutting down should the lamp behave erratically or fail to ignite

#### Applications

• Retail, Hospitality, Commercial, Institutional

# e-Vision TrakStick and Mini Square Electronic Ballasts

#### Ordering, Electrical and Technical Data (Subject to change without notice)

#### **Mini Square Ballasts**

| Lamp Data |           |                |                            | Certifi  | cations    |                           |                                   |                       |                 |      |                 |                                      |
|-----------|-----------|----------------|----------------------------|----------|------------|---------------------------|-----------------------------------|-----------------------|-----------------|------|-----------------|--------------------------------------|
| Number    | Watts     | Input<br>Volts | Catalog<br>Number          |          | F          | Line<br>Current<br>(Amps) | Input<br>Power<br>ANSI<br>(Watts) | Max.<br>Case<br>Temp. | Wiring<br>Diag. | Fig. | Weight<br>(lb.) | Max.<br>Distance<br>to Lamp<br>(ft.) |
| 20W La    | mp, ANSI  | Code M15       | 6/C156, Minimum Starti     | ng Temp. | -20°C/-4   | 4°F                       |                                   |                       |                 |      |                 |                                      |
| 1         | 20        | 120            | IMH-G20-G-LF or            | ~        | ~          | 0.20                      | 24                                | 90°C                  | 3               | G    | 0.90            | 5                                    |
|           | 20        | 277            | IMH-G20-G-BLS              |          |            | 0.09                      | 24                                | 90°C                  | 3               | G    | 0.95            | 5                                    |
| 39W La    | mp, ANSI  | Code M13       | 80/C130, Minimum Starti    | ng Temp. | -20°C/-4   | 4°F                       |                                   |                       |                 |      |                 |                                      |
| 1         | 39        | 120            | IMH-39-G-LF or             |          |            | 0.37                      | 44                                | 90°C                  | 3               | G    | 0.90            | 3                                    |
|           | 39        | 277            | IMH-39-G-BLS               | ~        | V          | 0.17                      | 43                                | 90°C                  | 3               | G    | 0.95            | 3                                    |
| 39W Mi    | ni Master | Color Lan      | np, CDM-Tm 35W/930, A      | NSI Code | e M179/C   | 179, Minii                | num Starti                        | ng Temp.              | -20°C/-4°F      |      |                 |                                      |
| 1         | 39        | 120            | IMH-P39-G-LF or            | ~        | ~          | 0.39                      | 46                                | 90°C                  | 3               | G    | 0.90            | 5                                    |
|           | 39        | 277            | IMH-P39-G-BLS              | ~        | ~          | 0.17                      | 45                                | 90°C                  | 3               | G    | 0.95            | 5                                    |
| 50W La    | mp, ANSI  | M110, C19      | 93 (Philips CDM Elite), Mi | nimum S  | tarting To | emp20°                    | C/-4°F                            |                       |                 |      |                 |                                      |
| 1         | 50        | 120            | IMH-50-G-LF or             | ~        | ~          | 0.47                      | 56                                | 90°C                  | 3               | G    | 0.90            | 3                                    |
|           | 50        | 277            | IMH-50-G-BLS               | ~        | ~          | 0.21                      | 55                                | 90°C                  | 3               | G    | 0.95            | 3                                    |
| 70W La    | mp, ANSI  | Code M9        | 8/C98 or M143 or M139/     | C139, Mi | nimum St   | arting Tei                | mp20°C/                           | -4°F                  |                 |      |                 |                                      |
| 1         | 70        | 120            | IMH-70-G-LF or             | ~        | ~          | 0.66                      | 79                                | 90°C                  | 3               | G    | 0.90            | 3                                    |
|           | 70        | 277            | IMH-70-G-BLS               | ~        | ~          | 0.28                      | 76                                | 90°C                  | 3               | G    | 0.95            | 3                                    |

#### **Trakstick Ballasts**

| Lamp    | o Data   |                |                           | Certifi   | cations    |                           |                                   |                       |                 |      |                 |                                      |
|---------|----------|----------------|---------------------------|-----------|------------|---------------------------|-----------------------------------|-----------------------|-----------------|------|-----------------|--------------------------------------|
| Number  | Watts    | Input<br>Volts | Catalog<br>Number         |           | F          | Line<br>Current<br>(Amps) | Input<br>Power<br>ANSI<br>(Watts) | Max.<br>Case<br>Temp. | Wiring<br>Diag. | Fig. | Weight<br>(lb.) | Max.<br>Distance<br>to Lamp<br>(ft.) |
| 20W La  | mp, ANSI | CodeM15        | 6/C156, Minimum Startin   | g Temp.   | -20°C/-4   | °F                        |                                   |                       |                 | 1    |                 |                                      |
| 1       | 20       | 120            | IMH-G20-E-LF              | ~         | ~          | 0.21                      | 24                                | 90°C                  | 3               | E    | 0.80            | 5                                    |
| I       | 20       | 277            |                           | V         | ~          | 0.09                      | 24                                | 90°C                  | 3               | E    | 0.80            | 5                                    |
| 39W La  | mp, ANSI | Code M13       | 0/C130, Minimum Starti    | ng Temp.  | -20°C/-4   | 4°F                       |                                   |                       |                 |      |                 |                                      |
| 1       | 39       | 120            | IMH-39-E-LF               | ~         | ~          | 0.38                      | 44                                | 90°C                  | 3               | E    | 0.80            | 5                                    |
|         | 39       | 277            |                           | ~         | ~          | 0.16                      | 43                                | 90°C                  | 3               | E    | 0.80            | 5                                    |
| 50W La  | mp, ANSI | M110, C19      | 3 (Philips CDM Elite), Mi | nimum S   | tarting To | emp20°                    | C/-4°F                            |                       |                 |      |                 |                                      |
| 1       | 50       | 120            | IMH-50-E-LF               | ~         | ~          | 0.48                      | 57                                | 90°C                  | 3               | E    | 0.80            | 5                                    |
| I       | 50       | 277            |                           | ~         | ~          | 0.20                      | 56                                | 90°C                  | 3               | E    | 0.80            | 5                                    |
| 70W Lai | mp, ANSI | Code M98       | 3/C98 or M143 or M139/0   | C139, Mir | nimum St   | arting Ter                | np20°C/-                          | 4°F                   |                 |      |                 |                                      |
| 1       | 70       | 120            | IMH-70-E-LF               | v         | ~          | 0.68                      | 80                                | 90°C                  | 3               | E    | 0.80            | 5                                    |
| I       | 70       | 277            |                           | ~         | ~          | 0.29                      | 78                                | 90°C                  | 3               | E    | 0.80            | 5                                    |

# e-Vision TrakStick and Mini Square Electronic Ballasts


#### Installation Notes


- 1. Red lead must be connected to center terminal of lamp (for Edison screw base lamps). Do not connect red or blue lead to neutral or ground.
- 2. Use an appropriately rated lamp holder.
- 3. Maximum ballast-to-lamp distance is provided in this bulletin as well as on each ballast's data sheet and label. For maximum lamp starting performance, this specification should be followed using typical wiring methods and materials.
- 4. Power mains must be cycled off and then on to reset ballast after failed lamps are replaced.

#### **Ballast Thermal Measurement Location**


Case temperature measurement locations differ with each ballast model and are designated on the individual ballast labels. Consult ballast labels and ballast specification sheets for measurement locations.

#### Dimensions





#### Wiring Diagram



| Case   | Overall | Case   | Case   | Case   | Mounting | Mounting |
|--------|---------|--------|--------|--------|----------|----------|
| Figure | Length  | Length | Width  | Height | Length   | Width    |
| E      | 140mm   | 127mm  | 44mm   | 30mm   | 135mm    | 26mm     |
|        | [5.5"]  | [5.0"] | [1.7"] | [1.2"] | [5.3"]   | [1.0"]   |
| G      | 97mm    | 90mm   | 77mm   | 30mm   | 87mm     | 67mm     |
|        | [3.8"]  | [3.5"] | [3.0"] | [1.2"] | [3.4"]   | [2.6"]   |

### e-Vision TrakStick and Mini Square Electronic Ballasts

#### Philips Advance Ballast Specifications

#### Section I - Physical Characteristics

1.0 The electronic ballast shall be furnished with integral, color-coded leads.

#### Section II - Performance Requirements

- 2.0 The electronic ballast shall operate from a nominal line voltage range of 120-277V, +/-10%, 50/60 Hz unless stated otherwise.
- 2.1 The electronic ballast input current shall have Total Harmonic Distortion (THD) of less than 15%.
- 2.2 The electronic ballast shall have a Power Factor greater than 90%.
- 2.3 The electronic ballast shall have a lamp end-of-life detection and shutdown circuit.
- 2.4 The electronic ballast shall be Sound Rated A.
- 2.5 The electronic ballast output frequency to the lamps shall be less than 200 Hz to prevent acoustic resonance inside the lamp arc tube and to minimize visible flicker.
- 2.6 The electronic ballast shall provide a "Lamp Current Crest Factor" of less than 1.5.
- 2.7 The electronic ballast shall be thermally protected to shut off when operating temperatures reach unacceptable levels.

#### Section III - Regulatory Requirements

- 3.0 The electronic ballast shall meet the requirements of the Federal Communications Commission rules and regulations, Title 47 CFR part 18, for Non-Consumer equipment.
- 3.1 The electronic ballast shall be Underwriters Laboratories (UL) Listed and CSA Certified where applicable.
- 3.2 Ballast shall comply with ANSI C62.41 Category A for transient protection.
- 3.3 Ballast shall comply with RoHS.

#### Section IV - Other

- 4.0 The electronic ballast shall not contain Polychlorinated Biphenyl (PCB's).
- 4.1 The electronic ballast shall carry a three-year limited warranty from the date of manufacture against defects in material or workmanship for operation at marked maximum case temperature or less. View limited warranty at http://www.usa. lighting.philips.com/connect/tools\_literature/ warranties.wpd for details and restrictions.
- 4.2 The manufacturer shall have a twenty-five year history of producing HID lamp ballasts for the North American market.
- 4.3 The electronic ballast shall be produced in a factory certified to ISO 9001 Quality System Standards.

Restrictions on Hazardous Substances (RoHS) is a European directive (2002/95/EC) designed to limit the content of 6 substances [lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls (PBB), and polybrominated diphenyl ethers (PBDE)] in electrical and electrical products. For products used in North America, compliance with RoHS is voluntary and self-certified.



© 2014 Koninklijke Philips N.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting North America Corporation 10275 W. Higgins Road, Rosemont, IL 60018 Tel: 800-322-2086 Fax: 888-423-1882 Customer Support/Customer Care: 800-372-3331

Imported by: Philips Lighting, A division of Philips Electronics Ltd. 281 Hillmount Rd, Markham, ON, Canada L6C 2S3 Tel. 800-668-9008