





# THE WORLD'S LIGHTEST 5-CHANNEL AND 3-CHANNEL CABLE PROTECTORS



**LOAD CAPACITY**  
Max load tested at 70°F (21°C)  
5,000 lb./Tire (2,267 kg)  
10,000 lb./Axle (4,534 kg)


RECESSED CARRYING HANDLE MOLDED IN TO THE UNDERSIDE OF THE PROTECTOR

5-CHANNEL CAPACITY = 1.25" OUTSIDE DIA.  
3-CHANNEL CAPACITY = 2.25" OUTSIDE DIA.



GRAINGER NUMBER	A: LENGTH	B: WIDTH	C: HEIGHT	D: CHANNEL WIDTH	E: CHANNEL HEIGHT
32RX20	36 in. (91.4 cm)	16.44 in. (41.76 cm)	1.59 in. (4.04 cm)	1.25 in. (3.18 cm)	1.25 in. (3.18 cm)

- The world's lightest 3 & 5-channel cable protectors by up to 75%!
- Connector System with easy hand-conforming grip
- Hinged lid. No fiberglass rod required to replace the lid.
- Patented\* 5-Bar tread pattern for maximum traction
- 5-channel protects cables and hoses up to 1.25" outside dia.
- 3-channel protects cables and hoses up to 2.25" outside dia..
- Made from tough, high impact absorbing, non-conductive polyurethane
- Resistant from oil, fuels and lubricants
- Recessed carrying handle molded in to the underside of the protector



GRAINGER NUMBER	A: LENGTH	B: WIDTH	C: HEIGHT	D: CHANNEL WIDTH	E: CHANNEL HEIGHT
32RX19	36 in. (91.4 cm)	18.21 in. (46.25 cm)	2.69 in. (6.83 cm)	2.25 in. (5.72 cm)	2.25 in. (5.72 cm)



For more information contact your Grainger Representative or visit [Grainger.com](http://Grainger.com)

AVAILABLE THROUGH

