



1001 Trout Brook Crossing
Rocky Hill, CT 06067-3910
Telephone: (860) 571-5100
FAX: (860) 571-5465

Product Description Sheet

Max Strength Headliner Adhesive

Maintenance, Repair & Operations, January 1999

PRODUCT DESCRIPTION

LOCTITE® Max Strength Headliner Adhesive is a high-strength and high temperature spray adhesive designed for bonding foam, carpet, fabrics, plastics, rubber, etc. This is due to the high strength and temperature resistance of the product.

PRODUCT BENEFITS

- Maintains high strength at temperatures up to 170°F(77°C)
- Resistant to extreme weather conditions
- Water resistant
- Dries clear
- VOC compliant

TYPICAL APPLICATIONS

- Headliners
- Carpets
- Trunk linings
- Door panels
- For use on foam, fabrics, plastics and rubber

DIRECTIONS FOR USE

1. Make sure all surfaces are clean, dry and free from any contaminants.
2. Shake can before use.
3. Turn nozzle to select spray pattern width; low, medium or high.
4. Hold can 6 to 8 inches from work surface and apply 2 to 3 uniform overlapping coats. Allow a minimum of 5 minutes drying time between coats. Apply additional coats in opposite direction from the first. For stronger bonds, apply adhesive to both surfaces.
5. Allow adhesive to dry for at least 5 minutes, or until tacky, before setting.
6. Press surfaces together with uniform pressure, eliminating air pockets. Bonds should be made within 30 minutes of application.
7. To prepare can for next use, invert and dispense until spray is free of adhesive.

For Cleanup

1. Clean hands with a dry cloth or hand cleaner.

PROPERTIES OF UNCURED MATERIAL

	Typical Value
Chemical Type	SIS Copolymer
Appearance	Aerosol spray
Odor	Solvent
Flash Point	Aerosol, contents under pressure, consult MSDS

TYPICAL ENVIRONMENTAL RESISTANCE

Temperature Resistance (max)	Typical Values
Continuous, °C (°F)	71 (160)

Chemical / Solvent Resistance

The product retains effective properties in contact with automotive fluids, such as motor oil, transmission fluids, alcohol and antifreeze solutions. Note: Not recommended for parts in contact with gasoline.

GENERAL INFORMATION

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials.

For safe handling information on this product, consult the Material Safety Data Sheet, (MSDS).

Storage

Products shall be ideally stored in a cool, dry location in unopened containers at a temperature between 8° to 28°C (46° to 82°F) unless otherwise labeled. Optimal storage is at the lower half of this temperature range. To prevent contamination of unused product, do not return any material to its original container. For specific shelf-life information, contact your local Technical Service Center.

Note

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. It is the user's responsibility to determine suitability for the user's purpose of any production methods mentioned herein and to adopt such precautions as may be advisable for the protection of property and of persons against any hazards that may be involved in the handling and use thereof. In light of the foregoing, **Loctite Corporation specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Loctite Corporation's products. Loctite Corporation specifically disclaims any liability for consequential or incidental damages of any kind, including lost profits.** The discussion herein of various processes or compositions is not to be interpreted as representation that they are free from domination of patents owned by others or as a license under any Loctite Corporation patents that may cover such processes or compositions. We recommend that each prospective user test his proposed application before repetitive use, using this data as a guide. This product may be covered by one or more United States or foreign patents or patent applications.

NOT FOR PRODUCT SPECIFICATIONS
THE TECHNICAL DATA CONTAINED HEREIN ARE INTENDED AS REFERENCE ONLY.
PLEASE CONTACT LOCTITE CORPORATION QUALITY DEPARTMENT FOR ASSISTANCE AND RECOMMENDATIONS ON SPECIFICATIONS FOR THIS PRODUCT.
ROCKY HILL, CT FAX: +1 (860)-571-5473 DUBLIN, IRELAND FAX: +353-(1)-451-9959