

EPOXY MAINTENANCE FLOOR COATING EASYCLEAR™



Warehousing



Storage facilities



Garages



Two-component system.
Convenient kit packaging.

High performance, easy maintenance flooring for mild to moderate environments

- Easy roller application
- Excellent protection over new or old concrete or previously coated floors
- Compliant Nationwide — <100 g/l VOC

RUST-OLEUM®



EPOXY MAINTENANCE FLOOR COATING

EASYCLEAR™

<100 VOC Epoxy Maintenance Floor Coating

Less Prep Time • Minimal surface prep, maximum adhesion.

Less Application Time • Easy brush and roller application. Convenient kit packaging.

Less Downtime • 10 hour light foot traffic; 24 hour normal foot traffic; 4 days vehicle traffic.

Greater Lifetime Value • Long lasting protection against dusting, staining, wear, chemicals and abrasion.

Typical applications

Interior concrete floors in mild to moderate industrial and commercial environments like:

Warehouses • Showrooms • Garages • Manufacturing • Storage Facilities

Kits (Contains base and activator. Combines to equal one gallon.)



1 gallon kit
Clear
#256673


Companion products



Anti-Skid Additive
#200504
For anti-slip



Minimal surface prep



Easy roller application



Long lasting protection

APPLICATION:



SUBSTRATES:



CONCRETE

Can be used in USDA-regulated facilities based on FSIS Directive 11,000.4 (Rev. 4), November 24, 1995. Agriculture Canada accepted.

RUST-OLEUM[®]
INDUSTRIAL BRANDS