



# CUSTOMER SPECIFICATION DRAWING



PART NUMBER	A	B	LENGTH ±2% [FEET]	MATERIAL	WEIGHT
GRC904	1/2	.015	50	304SS	1.31
GRC204		.030	50	200-300SS	2.50
GRC304		.030	50	GCS	2.47
GRC404		.030	50	316SS	2.53
GRC906	3/4	.015	50	304SS	1.96
GRC206		.030	50	200-300SS	3.75
GRC306		.030	50	GCS	3.70
GRC406		.030	50	306SS	3.70
GRC432	1-1/4	.044	50	201SS	9.26

**NOTES:**

1. MATERIAL PER BAND-IT SPECIFICATIONS.

ABOVE SPECIFICATION CERTIFIED BY: \_\_\_\_\_ DATE: \_\_\_\_\_

TITLE: \_\_\_\_\_

UNLESS OTHERWISE NOTED:  
DIMENSIONS ARE IN INCHES  
AFTER FINISH

TOLERANCES:  
X ..... ±0.100  
.XX ..... ±0.020  
.XXX ..... ±0.005  
.XXXX ..... ±0.001  
ANGLES ..... ±0.5°

**BAND-IT**®

A unit of ~~DEX~~ Corporation  
P.O. Box 16307  
Denver, Colorado U.S.A.

**PROPRIETARY AND CONFIDENTIAL**

THIS DRAWING WITH ALL  
CONTENTS IS PROPERTY OF  
BAND-IT. REPRODUCTION,  
DISCLOSURE OR MFG.  
OF MATTER SHOWN IS PROHIBITED  
WITHOUT WRITTEN PERMISSION.

DO NOT SCALE DRAWING

TITLE:

**ROLL BAND,  
GRAINGER**

DWG. NO.

**GRC202**

REV -

SHEET 2 OF 2