


Standard features

- Waterproof
- Impact resistant
- Conditional lifetime guarantee
- Crushproof
- Dustproof
- PowerclawTM latching system
- Soft grip foldable handle
- Lightweight NK-7TM resin
- Padlockable
- 100% stainless steel hardware
- High performance gasket
- Automatic pressure release valve
- Molded-in bezel system
- Integrated lid stay
- Stackable
- Meets airline carry-on regulations

Case specifications

| | |
|----------------------------|---|
| Exterior dimensions | L18.7" x W14.8" x H7.0" L475mm x W376mm x H178mm |
| Interior dimensions | L17.0" x W11.8" x H6.4" L432mm x W300mm x H163mm |
| Weight (empty) | 6.2 lbs 2.8 kg |
| Lid depth | 2.1" 53mm |
| Base depth | 4.3" 108mm |
| Material | lightweight NK-7 TM resin |
| Max buoyancy | 53 lbs 24 kg |
| Temperature range | Min -20°F (-29°C) Max 140°F (60°C) |
| Airline carry-on | yes |
| Watertight | yes |
| Warranty | conditional lifetime guarantee |

Available options



Certifications

| | |
|---------------------|---|
| ATA 300 | Impact test |
| ASTM D4169 | Falling rain - Vibration - Drop tests |
| MIL-STD-810F | Immersion test |
| IP 67 | Ingress protection tests (dust & immersion) |

Packaging specifications

| | |
|------------------------------|---|
| Quantity per pack | 1 |
| Pack dimensions | L18.9" x W14.9" x H7.2" L480mm x W380mm x H180mm |
| Pack weight (no foam) | 7.9 lbs 3.6 kg |

Available colors

