

ADDITIVE**RUST-OLEUM®****TECHNICAL DATA****RO-82****ALKYD ACCELERATOR****DESCRIPTION AND USES**

A clear liquid, isocyanate blend additive for low VOC alkyd coatings. Reduces the tack free dry time.

PRODUCTS

SKU	Description
239503	Alkyd Accelerator

PACKAGING

Quart containers

COMPANION PRODUCTS

3400 System High Performance 340 VOC Alkyd Enamel
2500 System High Performance 250 VOC Alkyd Enamel

PRODUCT APPLICATION

This material contains an isocyanate. Refer to the Material Safety Data Sheet for more information.

Add 4 ounces per gallon. Add the Alkyd Accelerator just prior to application of the coating. Mix well. Exceeding the recommended amount will not further enhance benefits. Apply the coating in the normal and recommended manner. Coating using the Alkyd Accelerator must be applied in 1-2 hours.

Opened containers of Alkyd Accelerator should be used within 2-4 weeks. Humidity will affect this material and reduce effectiveness. Do not use material if it has become cloudy.



PHYSICAL PROPERTIES

		ALKYD ACCELERATOR
Composition		Blend of Isocyanates
Solvents		N-Butyl Acetate, Light Aromatic Hydrocarbons
Weight	Per Gallon	9.11 lbs.
	Per Liter	1.09 kg
Solids	By Weight	82.8%
	By Volume	78.7%
Volatile Organic Compounds		<190 g/l (<1.58 lbs./gal.)
Pot Life		1-2 hours @ 70°F (21°C)
Shelf Life		1 year, unopened container
Safety Information		DANGER! VAPOR AND SPRAY MIST HARMFUL. OVEREXPOSURE MAY CAUSE LUNG DAMAGE. MAY CAUSE ALLERGIC SKIN AND RESPIRATORY REACTION, EFFECTS MAY BE PERMANENT. MAY AFFECT THE BRAIN OR NERVOUS SYSTEM CAUSING DIZZINESS, HEADACHE, OR NAUSEA. CAUSES EYE, SKIN, NOSE AND THROAT IRRITATION. READ LABEL INFORMATION. COMBUSTIBLE LIQUID AND VAPOR.

The technical data and suggestions for use contained herein are correct to the best of our knowledge, and offered in good faith. The statements of this literature do not constitute a warranty, express, or implied, as to the performance of these products. As conditions and use of our materials are beyond our control, we can guarantee these products only to conform to our standards of quality, and our liability, if any, will be limited to replacement of defective materials. All technical information is subject to change without notice.