

Nashua[®] TAPE PRODUCTS 324A

Cold weather UL 181A-P & B-FX Foil Tape



UL
Nashua[®] TAPE PRODUCTS
324A COLD WEATHER

Eco-Friendly
Release Liner





Nashua® TAPE PRODUCTS 324A

Cold weather UL181A-P & B-FX Foil Tape

Berry Plastics Corporation, the industry leader for innovative materials for HVAC, is proud to offer Nashua® 324A Cold weather UL181A-P & 181B-FX Listed Foil Tape. Designed to meet the needs of virtually all duct sealing applications, 324A is suitable for use on *fiberglass duct board, rigid sheet metal duct and flexible duct installations.*

SPECIAL FEATURES:

- UL181A-P and UL181B-FX Listed - Printed for easy identification
- UV Resistant
- Provides long-term anchorage and a durable seal
- Mold Resistant
- Humidity Resistant
- Superior cold weather adhesion (bonds down to -10° F)
- Excellent high temperature performance (up to 325° F)
- Eco-Friendly release liner made from unbleached natural kraft paper
- Low VOC (Volatile Organic Compounds)
- Can contribute toward EA Credit 1 (Optimize Energy Performance) and EQ Credit 4.1 (Low Emitting Materials, Adhesives and Sealants) under LEED®

Thickness: 4.8 mils (121.9 μ)

Adhesion to Steel: 68 oz/in (7.44 N/cm)

Adhesion to Backing: 60 oz/in (6.57 N/cm)

Tensile Strength: 27 lb/in (47.28 N/cm)

Installation Temperature Range: -10 to 200° F (-4 to 93° C)

Operating Temperature Range: -20 to 325° F (-29 to 110° C)

VOC Content: <30 g/L

NASHUA® 324A

2.5" x 60Yd

ITEM NO. 617022B

16 rolls/case

27 cases/pallet

UPC: 7-42366-00975-3

72mm x 55M

ITEM NO. 652231B

16 rolls/case

27 cases/pallet

UPC: 0-33656-31000-1

FOR MORE INFORMATION ON NASHUA® 324A OR OTHER NASHUA® BRAND PRODUCTS FOR THE HVAC MARKET, CONTACT YOUR AREA SALES REPRESENTATIVE.



Visit our website to learn more!

For more information:

25 Forge Parkway

Franklin, MA 02038

Phone 508.918.1600 • Fax 508.918.1901

Toll Free US: 1.800.343.7875

tapes.berryplastics.com

117_06-12