

Nashua[®]
TAPE PRODUCTS **330X**
Extreme Weather Foil Tape



Nashua® TAPE PRODUCTS 330X Extreme Weather Foil Tape

Berry Plastics Corporation, the industry leader for innovative materials for HVAC, is proud to offer Nashua® 330X Extreme Weather Foil Tape. Specially designed to meet the needs of cold weather applications, Nashua® 330X performs well in virtually all duct sealing applications and is suitable for vapor barrier sealing on ductwrap, FSK insulation, and fiberglass duct board.

SPECIAL FEATURES

- High adhesion and excellent “quick-stick”
- UL 723 Classified
- Resists UV, humidity and mold
- Provides long-term anchorage and a durable seal
- Eco-Friendly release liner made from unbleached natural kraft paper
- Superior cold weather adhesion (bonds down to -25° F)
- Broad performance temperature range (-35 to 260° F)
- Low VOC content
- Can contribute toward EA Credit 1 (Optimize Energy Performance) and EQ Credit 4.1 (Low Emitting Materials, Adhesives and Sealants) under LEED®

Thickness: 3.5 mils (88.9 μ)

Adhesion to Steel: 55 oz/in (6.02 N/cm)

Adhesion to Backing : 40 oz/in (4.38 N/cm)

Tensile Strength: 14 lb/in (24.52 N/cm)

Installation Temperature: -25 to 200° F (-37 to 93° C)

Operating Temperature: -35 to 260° F (-32 to 126° C)

VOC Content: <30 g/L



Visit our website
to learn more!



NASHUA® 330X EXTREME WEATHER FOIL

48mm x 46M
ITEM NO. 330015B
24 rolls/case
27 cases/pallet
UPC: 7-42366-00824-4

72mm x 46M
ITEM NO. 330017B
16 rolls/case
27 cases/pallet
UPC: 7-42366-00826-8

FOR MORE INFORMATION ON
NASHUA® 330X OR OTHER NASHUA®
BRAND PRODUCTS FOR THE HVAC
MARKET, CONTACT YOUR AREA SALES
REPRESENTATIVE.

For more information:
25 Forge Parkway
Franklin, MA 02038
Phone 508.918.1600 • Fax 508.918.1901
Toll Free US: 1.800.343.7875



tapes.berryplastics.com