

STI Universal Pneumatic Button



UB-1PN

PRODUCT OVERVIEW

The pneumatic button has a mechanical adjustable timer which opens or closes a circuit and has a timed delay before reset. It does not require power for actuation and has a timer life of over 1,000,000 operations. When local code or authority requires a pneumatic button be used, this device solves the problem.

Universal Pneumatic Button helps eliminate having to stock dozens of push buttons, and wasting precious time and money tracking down just the right button for a customer. It offers over 200 options to provide just what a customer wants in one convenient package. It is ready to be assembled out of box and is easily installed within minutes on site. The UB-1PN offers many different combinations for the price of a standard one configuration button. The faceplate is constructed of cast aluminum metal, allowing it to take tough knocks in stride, and is slightly oversized to cover old plate installation marks. Button package includes: faceplate, three push buttons, five button messages and seven changeable illuminated activation messages.

HOW IT WORKS

The installer simply has to choose which lens cover and interchangeable message plate works best for the customers need, and easily snap them in place. This allows the button to be mounted in a matter of minutes instead of waiting weeks for a specific button to be ordered and delivered.

FEATURES

- Pneumatic button offers many options to provide just what a customer wants in one convenient package.
- Mechanical adjustable timer opens or closes a circuit and has a timed delay before reset.
- Does not require power for actuation.
- Has a timer life of over 1,000,000 operations.
- Helps solve the problem of local code or authority requiring a pneumatic button be used.
- Offers over 200 different combinations.
- Faceplate constructed of cast aluminum.
- Pneumatic timer range: 2-60 seconds ($\pm 15\%$). Repeat accuracy $\pm 10\%$.
- Illuminated message light kit (requires 12-24 VDC/VAC).
- Independent Form "Z" contacts (one N.O., one N.C.) rated 10A @ 240 VAC.
- Operating Temperature is 15° to 120°F (-9° to 49°C).
- Three different lens covers included – red, green and blue.
- Five button messages included - Exit, Push, Push to Exit, handicap symbol and blank.
- Seven illuminated message inserts in green, blue, yellow, white and clear.
- Plate messages inscribed with EXIT and translucent blanks (allowing for custom labels).
- One year guarantee on electro mechanical and electronic components.

STI Universal Pneumatic Button

Dimensions and Technical Information

MODELS AVAILABLE

UB-1PN	Universal Pneumatic Button
UB-2PN	2" Universal Pneumatic Button
UB-1CL-Color	Custom Label applied to blank, changeable message plates (blue, green, white or yellow)
UB-2LENS	2" Lens Kit
SUB-UB-1C	Contact Block
SUB-71102A-Color	Color Match Back Box
STI-6518	Bopper Stopper® Protective Cover
STI-6600-Color	Mini Stopper® II with Horn (blue, green, white or yellow)


APPROVALS & WARRANTY

TESTING

It has been tested and approved or listed by:
· ADA for operation

WARRANTY

One year guarantee on electro mechanical and electronic components.



ILLUMINATED PUSH BUTTONS




ILLUMINATED MESSAGES



BUTTON MESSAGES





MESSAGE LIGHT KIT



FORM "Z" CONTACT BLOCK



MESSAGE LIGHT DIFFUSER



Safety Technology International, Inc.

2306 Airport Road
Waterford, Michigan
48327, USA

Tel: 248-673-9898
Fax: 248-673-1246
Toll-free: 800-888-4784
info@sti-usa.com
www.sti-usa.com

Unit 49G Pipers Road
Park Farm Industrial Estate
Redditch, Worcestershire
B98 0HU England

Tel: 44 (0) 1527 520 999
Fax: 44 (0) 1527 501 999
Free: 0800 085 1678 (UK)
www.sti-europe.com