



XX-Large Safe

S7371

Ideal for commercial office or home, the SentrySafe fire-safe features a 1-hour UL fire rating, combination with key lock, locking drawer, 2 multi-position shelves, 5 livelocking bolts and 3 dead bolts.



FEATURES:

- UL Classified for Fire Endurance (1-hour at 1700°F/927°C), to protect documents, records and valuables stored inside from fire damage
- For maximum protection 5 live-locking bolts and 3 dead bolts provide added security from invasion
- ETL Verified to withstand a 15-foot/4.5-meter drop during a fire and stay closed
- ETL Verified for 1-hour fire protection for digital media up to 1700°F/927°C in the event of a fire
- Dual combination lock and key increases security
- Adjustable locking drawer provides additional privacy
- 2 Adjustable shelves for easy and flexible organization
- Steel construction provides added security



Dimensions (H x W x D)

Exterior

39.8 in. x 25.4 in. x 23.4 in.
101.1 cm x 64.6 cm x 59.5 cm

Interior

30.7 in. x 18.7 in. x 13.8 in.
77.9 cm x 47.5 cm x 35.1 cm

Capacity

4.59 cu. ft.
129.81 liters

Product Weight

509 lbs.
230.9 kg