



XX-Large Safe

S6370

Ideal for commercial office or home, the SentrySafe fire-safe features a 1-hour UL fire rating, combination with key lock, locking drawer, multi-position shelf, 5 livelocking bolts and 3 dead bolts.



FEATURES:

- UL Classified for Fire Endurance (1-hour at 1700°F/927°C), to protect documents, records and valuables stored inside from fire damage
- For maximum protection 5 live-locking bolts and 3 dead bolts provide added security from invasion
- ETL Verified to withstand a 15-foot/4.5-meter drop during a fire and stay closed
- ETL Verified for 1-hour fire protection for digital media up to 1700°F/927°C in the event of a fire
- Dual combination lock and key increases security
- Steel construction provides added security



Dimensions (H x W x D)

Exterior

34.5 in. x 20.5 in. x 22.0 in.
87.6 cm x 52.1 cm x 55.9 cm

Interior

26.6 in. x 15.0 in. x 13.0 in.
67.6 cm x 38.1 cm x 33.0 cm

Capacity

3.01 cu. ft.
85.08 liters

Product Weight

335 lbs.
152.0 kg