SmartWasher[®] Industrial Grade Cleaning Solution

I. Product Description

CRC's SmartWasher® Industrial Grade Cleaning Solution is an aqueous, pH neutral, low VOC, non-corrosive, non-flammable, biodegradable cleaning fluid for use in the SmartWasher® Parts Washing System. The Solution works in conjunction with the Parts Washing System when warmed to 105° by the SmartWasher® units. The maximum strength, low odor Industrial Grade Cleaning Solution handles the removal of tough industrial soils as well as heavy grease, oil, carbon, sludge, dust and varnishes safely from all types of substrates.

The SmartWasher® System is a timely alternative to conventional petroleum-based solvent parts washers. SmartWasher® is a self-contained, self-cleaning system that is completely safe, nontoxic and generates no hazardous waste - without compromising cleaning ability. SmartWasher® uses the process of bioremediation - the accelerated breakdown of organic compounds such as grease, grime, varnish, oil, carbon and other heavy industrial soils through the use of microbes. The microbes, suspended in the Industrial Grade Cleaning Solution that recirculates through the unit, literally eat their way through soils, converting them into harmless water and Carbon Dioxide (CO₂). The solution remains clean and usable, unlike traditional solvent-based systems where the solution becomes dirty and less effective over time. Disposal becomes a nonissue, as hazardous waste streams are eliminated. This process is nonhazardous, non-caustic, nonflammable, and does away with the need for regulatory paperwork.

II. Applications

Recommended for parts cleaning in preventative maintenance and repair facilities, industrial manufacturing plants, automotive repair shops, metal fabricators, and anywhere that dirty, greasy, grimy parts need to be cleaned without regulatory or disposal issues. **SmartWasher® Industrial Grade Cleaning Solution** is safe to use on all types of metal parts and will not damage incidental components such as rubber or plastic.

Type of Soils	Industrial Grade Cleaning Ability
Motor Oil	Excellent
Bearing Grease	Excellent
Automotive Grease	Excellent
Impacted Grease	Excellent
Asphalt	Good
Creosote	Excellent
Resin Products	Excellent
Hydraulic/Transmission Fluid	Excellent

Type of Soils	Industrial Grade Cleaning Ability
Fifth Wheel Grease	Good
Crude Oil	Excellent
Solder & Flux	Excellent
Automotive Varnish	Good
Burned-on Carbon	Good
Cutting Oils	Fair
Ink/Toner	Good
Animal Fat	Excellent

III. Features & Benefits

- NSF A1 Registered.
- Environmentally preferred product. U.S. EPA Design for Environment (DfE) recognized.
- Industrial Grade. Removes the toughest industrial soils as well as lighter soils.
- Low Odor. Creates a more user-friendly working environment.
- Excellent Cleaning Ability. Cleaning Solutions contain wetting agents that literally lift soils off of parts to be rinsed away.
- Reduces the Risk of Hazardous Waste Disposal. SmartWasher® System generates no hazardous waste eliminating reporting, disposal and regulatory paperwork in most cases.
- Non-Corrosive. Will not scratch or score equipment finish. Contains flash rust inhibitors.
- Non-Flammable. Aqueous formulation reduces risk of fire and provides increased user safety.
- Neutral pH. Non-acidic and non-caustic.
- Contains Zero VOCs (volatile organic compounds, which cause ground smoq).
- No Class I or II Ozone Depleting Chemicals. Provides an alternative to 1,1,1-Trichloroethane products while complying with the EPA regulations on the use of ozone depleting chemicals.
- Available in 5 gallon pails for use in the SmartWasher® Parts Cleaning System.

IV. Physical Properties

Flash Point (TCC)	None
Odor	Minimal
Appearance	Light brown liquid
Vapor Density	>1 (Air = 1)
VOC Content (Fed)	0 g/L
Sara Title III, Sect. 313 Chemicals	None
Prop 65	None

Boiling Point	210°F
Freezing Point	ND
Solubility	Soluble in H ₂ O
Specific Gravity	1.0155
PH	8.02
Vapor Pressure	N.D.

V. Specifications and Approvals

- NSF Registration #143960, Category A1 for us in meat and poultry plants.
- Recognized by the U.S. Environmental Protection Agency Design for the Environment (DfE) Formulator Initiative.

VI. Performance Characteristics

Filtration*	user changeable without hand tools or special equipment	
	user disposable	
	microbe impregnated	
	filtration to 50 microns	
Microbe Treatment*	environmental-shock resistant	
	preserved for 18 month minimum shelf life	
	suspended ion filter with water-soluble material for release at a predictable rate	
	Nonpathogenic	

^{*}Filtration and microbial properties indicative of total system use

VII. Directions

- * Read the Operating Manual included with each SmartWasher® unit for installation information.
- * Initial start-up requires 25 gallons of fluid and one filter in addition to the unit.
- * Fluid replenishment is one 5 gallon pail every 6 to 8 weeks or as needed; filter replacement is one per month.
- * Once installed, the SmartWasher® should be left plugged in and turned on, even when not washing parts. In the Standby/Ready mode the fluid will be kept at the recommended operating temperature. If the temperature falls below the recommended minimum, the system will still clean, but the remediation of the hydrocarbons by the microbe colony will slow down. The microbes will reactivate when the fluid temperature reaches the appropriate level.

VIII. Package Description

Part Number	Container Size
14148	5 Gallon Pail

IX. Disposal

Disposal requirements vary by state and local jurisdiction. All used and unused product should be disposed of in conformance with local, state and federal regulations.

X. Special Use Warnings

Genera

Avoid direct skin contact or inhalation. Allergic reactions to industrial products may occur in some individuals. It is recommended that safety glasses and rubber gloves be worn when handling industrial use products.

SmartWasher® and ChemFree® are registered trademarks of ChemFree® Corporation.

<u>DISCLAIMER</u>: This information is accurate to the best of CRC Industries' knowledge or obtained from sources believed by CRC to be accurate. Before using any product, read all warnings and directions on the label. All products should be tested for suitability on a particular application prior to actual use. CRC Industries, Inc. makes no representations or warranties of any kind concerning this data.

CRC Industries, Inc. Industrial Products Division Warminster, PA 18974
Technical Service: (800)521-3168 Customer Service: (800)272-4620 CRC On-Line: (215)442-6260

Literature Reorder #TDS208 CRC On-Line # 208 REV. 6/11