



CODE (1)	AUX CONTACTS		TYPE OF CONNECTION	MAX CURRENT		MAXIMUM HORSEPOWER RATINGS					
	NO	NC		INDUCTIVE	RESISTIVE	1Ø		3Ø			
				AC3 (A)	AC1 (A)	115 V	230 V	200 V	230 V	460 V	575 V
0610	1	—	SCREW-CLAMP	6	15	0.5	1	1.5	1.5	3	3
0601	—	1									
0910	1	—	SCREW-CLAMP	9	20	0.5	1.5	2	3	5	5
0901	—	1									
1210	1	—	SCREW-CLAMP	12	20	0.5	1.5	3	3	7.5	10
1201	—	1									

(LC1 KO) AC CONTACTORS			(LP1 KO) DC CONTACTORS		(LP4 KO) DC CONTACTORS LOW CONSUMPTION	
VOLTS AC 50/60 HZ	CODE (2)		VOLTS DC	CODE (2)	VOLTS DC	CODE (2)
12	J7		12	JD	12	JW3
24	B7		20	ZD	24	BW3
36	C7		24	BD	48	EW3
42	D7		36	CD	72	SW3
48	E7		48	ED		
110	F7		60	ND		
127	FC7		72	SD		
220/230	M7		100	KD		
230	P7		110	FD		
230/240	U7		125	GD		
380/400	Q7		200	LD		
400	V7		220	MD		
400/415	N7		230	MPD		
440	R7		240	MUD		
500	S7		250	UD		
660/690	Y7					



Catalog Number: LC1 K(1)X(2), LP1 K(1)X(2), LP4 K(1)X(2)
Ratings: SEE CHART
UL File/CCN: —
CSA File/Class: —
Meets Standards: IEC 947, NF C 63-140, VDE 0660, BS 5424
Weight: —
Wire Size: AWG 16-10
Terminal torque: 7 LB-IN
Mounting Hwd: 35mm DIN rail, #8 screws

THE SQUARE D COMPANY HAS PROPRIETARY RIGHTS TO THE INFORMATION CONTAINED HEREON. THIS INFORMATION REMAINS THE PROPERTY OF SQUARE D COMPANY AND MAY BE USED ONLY IN CONFORMANCE WITH INSTRUCTIONS ISSUED BY SQUARE D COMPANY. USER SHOULD VERIFY DRAWINGS ARE TO THE LATEST/CURRENT REVISION PRIOR TO INCORPORATING IN A DESIGN FILE.

DO NOT SCALE DRAWING
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES

THIRD ANGLE PROJECTION
TOLERANCES
UNLESS OTHERWISE SPECIFIED
2 PLACE DECIMALS ± .01

IEC CONTACTOR
NON-REVERSING (K-LINE)
LC1 K(1)(2), LP1 K(1)(2), LP4 K(1)(2)

SQUARE D COMPANY

DWG# E021001-01
NO.