



A Brand of **rrwDevcon**

30 Endicott St.
Danvers, MA 01923 USA
Telephone: 978-777-1100
Toll Free: 800-933-8266

Technical Data Sheet

Permatex® Pipe Joint Compound

INDUSTRIAL

PRODUCT DESCRIPTION

S.I.N.: 834-300

Permatex® Pipe Joint Compound is a black, viscous, brushable liquid sealant and lubricant designed to help assemble and seal threaded joints on water, steam, oil and fuel lines.

PRODUCT BENEFITS

- Non-hardening for easy disassembly
- Works to 400°F (204°C)
- Sealing pressures to 5000 psi (100 psi for steam)
- Outperforms Teflon tape and does not shred
- No measuring or mixing
- Prevents galling and corrosion

TYPICAL APPLICATIONS

- Threaded pipe
- Pipe fittings
- Flanges

DIRECTIONS FOR USE

1. Clean threads to be sealed. A light coating of oil or grease will not affect the sealability.
2. Apply the compound to the male threads, brushing into the grooves of the threads.
3. Assemble the parts.
4. On flanges and gaskets, apply a thin coat to each surface.
5. Let stand for 5 minutes and then assemble

For Cleanup

1. Clean up with isopropyl alcohol.
2. Clean hands with a dry cloth or Permatex® Fast Orange® hand cleaner.

PROPERTIES OF UNCURED MATERIAL

	Typical Value
Chemical Type	Polymerized vegetable oil
Appearance	Black viscous liquid
Odor	Alcoholic
Specific Gravity	1.28
Viscosity	Flow similar to mustard
Flash Point, TCC, °F	76

TYPICAL CURING PERFORMANCE

Permatex® Pipe Joint Compound cures by the evaporation of solvent. Full properties will be affected in 24 hours.

PERFORMANCE OF CURED MATERIAL

Forms a semi-liquid, flexible seal when fully cured.
Temperature range -65°F to +400°F (-54°C to +204°C)

GENERAL INFORMATION

This product is not recommended for use in pure oxygen and/or oxygen rich systems and should not be selected as a sealant for chlorine or other strong oxidizing materials.

For safe handling information on this product, consult the Material Safety Data Sheet, (MSDS).

ORDERING INFORMATION

Part Number	Container Size
80045 (51D)	16 oz. bottle

STORAGE

Products shall be ideally stored in a cool, dry location in unopened containers at a temperature between 8° to 28°C (46° to 82°F) unless otherwise labeled. Optimal storage is at the lower half of this temperature range. To prevent contamination of unused product, do not return any material to its original container

NOTE

The data contained herein are furnished for information only and are believed to be reliable. We cannot assume responsibility for the results obtained by others over whose methods we have no control. **Permatex, Inc. specifically disclaims all warranties expressed or implied, including warranties of merchantability or fitness for a particular purpose, arising from sale or use of Permatex, Inc. products and disclaims any liability for consequential or incidental damages of any kind, including lost profits.** This product may be covered by one or more United States or foreign patents or patent applications

NOT FOR PRODUCT SPECIFICATIONS.
THE TECHNICAL DATA CONTAINED HEREIN ARE INTENDED AS REFERENCE ONLY.
PLEASE CONTACT PERMATEx, INC., TECHNICAL SERVICE DEPARTMENT FOR ASSISTANCE AND RECOMMENDATIONS FOR YOUR SPECIFIC APPLICATION.
PERMATEx, INC., HARTFORD SQUARE NORTH, 10 COLUMBUS BOULEVARD, HARTFORD, CT 06106 PHONE - (1-877PERMATEx) 09/02