



Technical Characteristics

For Use With	For use on 3 phase 600Vac phase-to-ground maximum (do not use on ungrounded systems)
Height	Use for pumps, motor applications and service-entrance locations
Enclosure Rating	NEMA 4 rated enclosure
Hub Opening	3.1
Joules	1304
Manufacturer Warranty	Square D warrants equipment manufactured by it and sold through authorized sales channels to be free from defects in materials and workmanship for two (2) years from date of invoice by Square D or its authorized retail channel.
Approvals	ANSI certified and CSA- and UL 1449 3rd Edition listed
Ampere Rating	36000 A
Application	Provides equal protection to all circuits and receptacles
Full Capacity Taps	For use on 3 phase 600Vac phase-to-ground maximum (do not use on ungrounded systems)
Depth	3.4
Jaw Release	ANSI certified and CSA- and UL 1449 3rd Edition listed
Interrupting Rating	Provides equal protection to all circuits and receptacles
General Application	Use for pumps, motor applications and service-entrance locations
Insulation Temperature	36000 A
Wire Binding	Provides equal protection to all circuits and receptacles
Winding Material	36000 A
Socket Type	For use on 3 phase 600Vac phase-to-ground maximum (do not use on ungrounded systems)
Terminal Type	3.1
Specifications	Use for pumps, motor applications and service-entrance locations
Pressure Setting	3.4
Service (Type of Feed)	NEMA 4 rated enclosure
Wire Size	ANSI certified and CSA- and UL 1449 3rd Edition listed

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.

Generated: 08/03/2015 14:18:35