

Z-Line Shelving

Easy Assembly

Two way keyhole slots and snap-in rivet design make installation a snap. No clips, sway braces, corner gussets or additional hardware needed.

Structural Integrity

Positive rivet connection combines with 14 gauge angle post to make a rigid framework ideal for mezzanine or high density mobile shelving.

Tall, Upright Posts

Upright posts are available in lengths up to 181½".

Added Reinforcement

Handle extra heavy loads with extra center support.

Strength Without Compromise

Standard 14 gauge double rivet beam has 2¾" profile and handles loads up to 2000 lbs. Or choose our optional 3¼" profile channel beam for even greater load capacity.

Long Spans

Configure units up to 96" wide by 60" deep with Z-Line's channel beams.

Flexible Design

Shelves adjust in 1½" increments for optimum flexibility.

Flattened Keyhole Slot



Positioning shelves is easy, with a special flattened locator keyhole in every fourth position.

Low Profile Shelf Support

Maximize shelf openings with thin but strong shelf supports.

Medium Shelf Support

Special V-beam design provides heavy-duty support at an affordable price.

Wide Profile Shelf Support

Heavy-duty 2¾" high beam laterally supports in longer spans and can accommodate up to 2,500 lbs. depending on shelf size.

Strong, Economical Shelves

Industrial grade particle board shelves hold up to the toughest applications — at an affordable price.



Z-Line Shelving

When it comes to value without compromising performance, you're talking about Z-Line shelving. Its fastening mechanism combined with a versatile array of components means it fits all your storage needs. The interlocking keyhole design not only makes installation fast and easy but eliminates the need for clips, gussets, sway braces or other hardware necessary with conventional shelving. Without these obstacles you have completely free access from all sides of the unit. Z-Line's adaptability makes it ideal for any size storage requirement. Its interchangeable componentry means it can be configured for single width shelving applications or spans up to 96" wide. It's a multifaceted system that affordably solves all your storage needs.

Low Profile Shelving Unit



Tennsco Low Profile Shelving Units are your solution when you need to maximize vertical storage space and need unobstructed access to stored items. The specially designed shelf supports with particle board are only 1 1/8" tall yet handle load capacities from 600-800 lbs depending upon the steel-gauge and shelf size you select. Widths available up to 48".

Medium Profile Shelving Unit



Tennsco Medium Profile Shelving Units incorporate a special 2 1/4" high v-beam design offering heavy-duty support at an economical price. With the added load capacity you'll find hundreds of uses in your factory or warehouse. Shelf supports are available in either 16 or 14 gauge steel to handle shelf load capacities ranging from 600 to 1,000 lbs. depending upon the gauge and shelf size selected. Widths available up to 72".

Exceptional Strength



Double rivet design and keyhole slots form a rigid framework. Combine heavy gauge steel posts, shelf supports and angle beams and you have a shelving system that easily stands up to any industrial application.

Easy Assembly



Assembly goes smoothly and quickly with Z-Line's snap-in rivet and keyhole design that eliminates the need for fasteners or braces.